









ALL HOLES
⌀ 0.1



- 1 INTERFACE DESIGN ARE LEFT TO TE CONNECTIVITY
△ CENTER OF GRAVITY
3 ALL DIMENSIONS IN () FOR INFORMATION ONLY
4 SOLDERING PROCESS: LEAD FREE REFLOW SOLDERING IN REFERENCE TO JEDEC J-STD-020D
△ VACUM GRIP AREA FREE OF SCRATCH
6 2333982-2 CODE B AS SHOWN
△ PCB TOP LAYER MUST BE GND PLANE, EXCEPT THE NEED SIGNAL PATHES AND CUT OUT AREAS
8 MATED WITH TE PLUG 2324319-X OR 2324309-X
△ MATERIAL MARKING, EXCHANGEABLE SEE TABLE
△ THE ONLY DIFFERENCE OF UAES P/N COMPARED TO GENERAL ONES IS SPECIAL LABEL USED ON PACKAGE, COMPONENTS ARE EXACTLY SAME ACCORDINGLY



/	2-2333982-9	Z	A	4	SHIELD	STAINLESS STEEL	5.99	Ni/Sn	3
			A	6	NANO MQS TAB	BRASS		Ni/Sn	2
			A	1	3 PORT 90° HSG COD. Z	PA10T-GF30		WATER BLUE	1
/	2-2333982-7	J	A	4	SHIELD	STAINLESS STEEL	5.99	Ni/Sn	3
			A	6	NANO MQS TAB	BRASS		Ni/Sn	2
			A	1	3 PORT 90° HSG COD. J	PA10T-GF30		BEIGE	1
/	2-2333982-3	C	A	4	SHIELD	STAINLESS STEEL	5.99	Ni/Sn	3
			A	6	NANO MQS TAB	BRASS		Ni/Sn	2
			A	1	3 PORT 90° HSG COD. C	PA10T-GF30		BLUE	1
/	2-2333982-2	B	A	4	SHIELD	STAINLESS STEEL	5.99	Ni/Sn	3
			A	6	NANO MQS TAB	BRASS		Ni/Sn	2
			A	1	3 PORT 90° HSG COD. B	PA10T-GF30		WHITE	1
/	2-2333982-1	A	A	6	NANO MQS TAB	BRASS	5.99	Ni/Sn	3
			A	1	3 PORT 90° HSG COD. A	PA10T-GF30		BLACK	1
			A	4	SHIELD	STAINLESS STEEL		Ni/Sn	3
/	1-2333982-9	Z	A	6	NANO MQS TAB	BRASS	6.3	Ni/Sn	2
			A	1	3 PORT 90° HSG COD. Z	PA4T-GF30		WATER BLUE	1
			A	4	SHIELD	STAINLESS STEEL		Ni/Sn	3
/	1-2333982-7	J	A	6	NANO MQS TAB	BRASS	6.3	Ni/Sn	2
			A	1	3 PORT 90° HSG COD. J	PA4T-GF30		BEIGE	1
			A	4	SHIELD	STAINLESS STEEL		Ni/Sn	3
/	1-2333982-3	C	A	6	NANO MQS TAB	BRASS	6.3	Ni/Sn	2
			A	1	3 PORT 90° HSG COD. C	PA4T-GF30		BLUE	1
			A	4	SHIELD	STAINLESS STEEL		Ni/Sn	3
/	1-2333982-2	B	A	6	NANO MQS TAB	BRASS	6.3	Ni/Sn	2
			A	1	3 PORT 90° HSG COD. B	PA4T-GF30		WHITE	1
			A	4	SHIELD	STAINLESS STEEL		Ni/Sn	3
3-2333982-1	1-2333982-1	A	A	6	NANO MQS TAB	BRASS	6.3	Ni/Sn	2
			A	1	3 PORT 90° HSG COD. A	PA4T-GF30		BLACK	1
			A	4	SHIELD	BRASS		PRE-TIN	3
/	2333982-9	Z	A	6	NANO MQS TAB	BRASS	6.3	Ni/Sn	2
			A	1	3 PORT 90° HSG COD. Z	PA4T-GF30		WATER BLUE	1
			A	4	SHIELD	BRASS		PRE-TIN	3
/	2333982-7	J	A	6	NANO MQS TAB	BRASS	6.3	Ni/Sn	2
			A	1	3 PORT 90° HSG COD. J	PA4T-GF30		BEIGE	1
			A	4	SHIELD	BRASS		PRE-TIN	3
/	2333982-3	C	A	6	NANO MQS TAB	BRASS	6.3	Ni/Sn	2
			A	1	3 PORT 90° HSG COD. C	PA4T-GF30		BLUE	1
			A	4	SHIELD	BRASS		PRE-TIN	3
/	2333982-2	B	A	6	NANO MQS TAB	BRASS	6.3	Ni/Sn	2
			A	1	3 PORT 90° HSG COD. B	PA4T-GF30		WHITE	1
			A	4	SHIELD	BRASS		PRE-TIN	3
/	2333982-1	A	A	6	NANO MQS TAB	BRASS	6.3	Ni/Sn	2
			A	1	3 PORT 90° HSG COD. A	PA4T-GF30		BLACK	1
			A	4	SHIELD	BRASS		PRE-TIN	3

TE ASSY NO. FOR UAES △	TE ASSY NO.	CODING	REV	QTY	DESCRIPTION	MATERIAL	WEIGHT (G)	FINISH/ COLOUR	PO S.
THIS DRAWING IS A CONTROLLED DOCUMENT.					DATE 29JAN2023	BY JL EU	CHKD D. ZHJL	DATE 29JAN2023	BY F. DEAN
DIMENSIONS (MM)					0 PLG 1 PLG 2 PLG 3 PLG 4 PLG	±0.3 ±0.20 ±0.20 ±0.20 ±0.20	±0.3 ±0.20 ±0.20 ±0.20 ±0.20	±0.3 ±0.20 ±0.20 ±0.20 ±0.20	±0.3 ±0.20 ±0.20 ±0.20 ±0.20
MATERIAL					FINISH	WEIGHT	SCALE	5:1	SHEET 1 OF 1
CUSTOMER DRAWING					NAME	3-PORT MATENET HDR ASSY 90DEG	SIZE	CASE CODE	DRAWING NO
					DATE	29JAN2023	REV	A	00779
					REV	C	2333982		