

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

REVISIONS



© COPYRIGHT - TE Connectivity Ltd.

ALL RIGHTS RESERVED.


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL DRAWN	09AUG2019	RV	DH

Ordering Information

Part Number	Nominal Voltage	Pick-Up (V)	Drop-Out Range (V)
VMAXEA	24VAC	21	15 to 20
VMAXAA	120VAC	104	78 to 99
VMAXBA	240VAC	209	156 to 199
VMAXOA	24VDC	21	15 to 20
VMAXNA	48VDC	42	31 to 40
VMAXPA	125VDC	109	81 to 103



Wiring Diagram (Bottom View)



Outline Dimensions

ALL DIMENSIONS ARE IN INCHES(MM).

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	RV	09AUG2019	 TE Connectivity	NAME	VMA SERIES UNDERVOLTAGE RELAY			
DIMENSIONS: INCHES		CHK	RV	09AUG2019			PRODUCT SPEC	-		
		APVD	DH	09AUG2019			APPLICATION SPEC	-		
TOLERANCES UNLESS OTHERWISE SPECIFIED:					SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
0 PLC ± -					A3	-	©=VMA-SERIES	-		
1 PLC ± -					CUSTOMER DRAWING	SCALE	NTS	SHEET	1 of 1	
2 PLC ± -							REV	A		
3 PLC ± -										
4 PLC ± -										
ANGLES ± -										
FINISH										
MATERIAL										