












REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
6		ECR-21-102340	21APR2021	F.F	M.S

- NOTE:
- 1. MATERIAL: COPPER ALLOY
THICKNESS: 0.15MM
 - 2. PLATING:
TIN PLATING OVER NICKEL PLATING OVERALL
 - 3. PART NUMBER ABBREVIATION ON BOTH SIDES.
 - 4. PACKAGED IN REEL INSIDE OF CARTON.



0.95...1.30 mm	0.22...0.35 mm ²	2834464-6
0.85...1.10 mm	0.13...0.17 mm ²	2834464-5
INSUL.DIA ISOØ	WIRE-SIZE DGB	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN. FRANK FAN 21APR2021	TE Connectivity	
DIMENSIONS: mm		CHK. GEORGE FU 21APR2021		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD. MING SHI 21APR2021	NAME SOCKET CONTACT FOR MINIDYNAMIC	
0 PLC ±0.5		PRODUCT SPEC		
1 PLC ±0.3		108-137443	SIZE CAGE CODE DRAWING NO. RESTRICTED TO	
2 PLC ±0.15		APPLICATION SPEC		
3 PLC ±		114-137526	A 00779 ©=2834464	
4 PLC ±		WEIGHT		
ANGLES FINISH		CUSTOMER DRAWING	SCALE 7:1 SHEET 1 OF 1 REV 6	