

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL DRAWING	12SEP2019	VM	DH

Part Numbering System

Typical Part Number 6001 -6002 C

Model Number:
6001 = Fixed timer, -55°C to +125°C


Timing Code:
Four-digit code for any value between 50ms and 600s.

The timing code consists of four digits and gives the time in ms. The first three digits are the significant figures and the last digit is the number of zeros following the significant figures; thus 50 ms would be coded 0500, 1.1 s would read 1101, and 1 m (60 s) would be 6002.

Optional Suffix:
C = Commercial version equivalent to M83726/13.


A typical part number would be 6001-6002C. This solid state output timing module has a time delay of 60s at 28Vdc and is the commercial equivalent to M83726/13.

Outline Dimensions



COLORED BEAD

14 PINS GOLD PLATE PER MIL-G-45204, TYPE II, CLASS I, UNDERPLATING, NICKEL 50 TO 150 MICRONS THICK. 3 TERMINALS FOR CIRCUIT CONNECTIONS



Product Facts

- Fixed delay on operate timer
- 300mA output
- CMOS digital design
- Voltage surge protection
- Qualified to MIL-R-83726/13

Electrical Specifications

Timing Range — 50 ms to 600 s.
Timing Accuracy — ±10% of nominal timing under all conditions of input voltage and environmental extremes

Recycle Characteristics —
Before Time Out — A power interruption occurring after the start but before completion of the timing cycle shall be for a duration of 0.5% of the nominal time delay or 10ms, whichever is greater, to ensure a loss in timing of no greater than 10%

After Time Out — A power interruption of 0.5% of the nominal time delay or 10ms, whichever is greater, will initiate a new timing cycle with a loss in timing of no greater than 5%

Special Notes:

- Load is connected between B+ and terminal designated. Delay begins upon application of power to terminals (B+ and B-).
- Always consult latest military specification for changes and additional information.

Input Data

Input Voltage — 28Vdc, nominal; range 18 to 31Vdc
Current Drain (at 25°C, 28Vdc) — 10mA (max.), plus load current
Reverse Polarity Protection — The timer will not be damaged or operate when input voltage polarity is reversed

Output Data

Configuration — 1 Form A (SPST-NO) solid state switch closure to ground

Load Ratings

Resistive — 300mA @ +25°C, derated to 100mA @ +125°C
Inductive — Three MIL-R-5757/9 relays (any relay with 26.5Vdc coil)
Lamp Load — Two MS25237-327 lamps per MIL-L-6363

Load Suppression — Suppression for inductive loads for output protection is provided within the unit

Voltage Drop — 2.5Vdc, max. @ -55°C and +25°C; 2.0 Vdc, max., @ +125°C

Leakage Current — 1µA, max. @ +25°C, 10µA, max. @ +125°C

Insulation Resistance — 1,000 megohms, min., @ 500Vdc, measured between all terminals tied together to the case

Dielectric Strength — 500Vrms, 60 Hz., at sea level, measured between all terminals tied together to the case

Transients —
Voltage Surge — Per MIL-STD-704A, figure 9, limit 1, for category B equipment
Self-generated Spikes — ±10V

Environmental Specifications

Temperature Range — -55°C to +125°C
Altitude — 80,000 ft.

Shock — 150 G's, 11 ± 1ms half-sine wave

Vibration (sinusoidal) — 10 -80 Hz. at 0.06 inch DA; 80 - 3,000 Hz. at 20 G's


Sealing — MIL-STD-202, method 112, condition C

Materials:
Cover — Nickel
Header — Kovar® Alloy
Pins — Kovar® Alloy, gold plated

Marking — Per MIL-R-83726

Weight — 0.42 oz (12g) max.

Timing Diagram



Environmental Specifications

Temperature Range — -55°C to +125°C

Altitude — 80,000 ft.


Shock — 150 G's, 11 ± 1ms half-sine wave

Vibration (sinusoidal) — 10 -80 Hz. at 0.06 inch DA; 80 - 3,000 Hz. at 20 G's

Sealing — MIL-STD-202, method 112, condition C

Materials:
Cover — Nickel
Header — Kovar® Alloy
Pins — Kovar® Alloy, gold plated
Marking — Per MIL-R-83726
Weight — 0.42 oz (12g) max.

Wiring Diagram



PIN 10 IS ACTIVE. DO NOT CONNECT.

ALL DIMENSIONS ARE IN INCHES(MM)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN VM 12SEP2019	TE Connectivity		
		CHK RV 12SEP2019			
		APVD DH 12SEP2019	NAME		
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		6001 SERIES DELAY ON OPERATE DIGITAL TIMING MODULE	
		0 PLC ± -	PRODUCT SPEC		
		1 PLC ± -	APPLICATION SPEC		
		2 PLC ± -	SIZE		
		3 PLC ± -	CAGE CODE		
		4 PLC ± -	DRAWING NO		
		ANGLES ± -	RESTRICTED TO		
MATERIAL		FINISH	A3 - C-6001-SERIES		
			WEIGHT		
			CUSTOMER DRAWING		
			SCALE	SHEET	REV
			NTS	1 OF 1	A