

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - TE Connectivity Ltd. ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	A	INITIAL DRAWING	14AUG2019	VM TN

### Ordering Information

Sample Part Number **▶**

**WOUF -12 -5060 -T**

Type:

WOUF = Over/Underfrequency

Input Voltage (VAC)


- 12 = 120
- 23 = 230
- 38 = 380
- 46 = 460

Frequency Range


	UF Adj.	OF Adj.
50 =	40-50 Hz	50-60 Hz
60 =	50-60 Hz	60-70 Hz
400 =	350-400 Hz	400-450 Hz

Time Delay Options

- blank = Per Time Curve
- T = Adjustable



Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.



SINGLE PHASE MODULES

ALL DIMENSIONS ARE IN INCHES

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN VM 14AUG2019	TE Connectivity		
DIMENSIONS: INCHES		CHK RV 14AUG2019			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD TN 14AUG2019	PRODUCT SPEC		
0 PLC ± -		APPLICATION SPEC			
1 PLC ± -		SIZE A3			
2 PLC ± -		CAGE CODE -			
3 PLC ± -		DRAWING NO C-WOUF-SERIES			
4 PLC ± -		RESTRICTED TO -			
ANGLES ± -		WEIGHT -			
MATERIAL -		CUSTOMER DRAWING			
FINISH -		SCALE NTS		SHEET 1 OF 1	
				REV A	