

REVISIONS							
REV	DESCRIPTION	DATE	APPV				
А	PRODUCTION RELEASE	JHAGER 3/23/22					





NOTES: (UNLESS OTHERWISE SPECIFIED)

- 1. ALL DIMENSIONS ARE IN MILLIMETERS [IN].
- 2. DIMENSIONS APPLY AFTER FINISHING.
- 3. MANUFACTURE TO BE COMPLIANT WITH EU RoHS DIRECTIVE, USE MATERIALS THAT DO NOT CONTAIN REACH SUBSTANCES OF VERY HIGH CONCERN >1000ppm, AND USE DRC CONFLICT-FREE SOURCED MATERIALS.
- 4. ELECTRICAL PROPERTIES SHOWN FOR REFERANCE ONLY. SEE LINX DATA SHEET FOR COMPLETE SPECIFICATIONS:
 - 1. IMPEDANCE: 50Ω
 - 2. FREQUENCY: 2.4GHz
 - 3. VSWR: NTE 2.5
- 5. ANTENNA QUALIFIED IAW LINX INTERNAL TEST PLAN AT LATEST REVISION.
- 6. MECHANICAL PROPERTIES:
 - 1. USE TEMPERATURE: [SEE MATERIAL PROPERTIES]
 - 2. BREAK AND DEBURR ALL SHARP EDGES
- 7. PACKAGE ANTENNAS INDIVIDUALLY IN TRAY BEFORE PLACING IN LOT BAG. LABEL ALL LOT BAGS, TRAYS AND BOXES WITH THE FOLLOWING INFORMATION ONLY:
 - 1. LOT NUMBER
 - 2. LINX PART NUMBER
 - 3. QUANTITY
 - 4. COUNTRY OF ORIGIN

THAT IS THE SOLE PRO TREATED AS SUCH. DOCUMENT IS PERM	AWING CONTAINS PROPRIETAR OPERTY OF LINX TECHNOLOGIES NO DISCLOSURE OR REPRODU(IITTED, IN WHOLE OR IN PART, PERMISSION OF LINX TECHNOL DESIGNATED AGENTS.	TITLE:					
MATERIAL: SUS430	INTERPRET DIMENSIONS AN TOLERANCES PER ASME Y14 .X ±2.0 ANGLES:	4.5. PROJECTION	ANT 2.4GHz METAL STAMP				
FINISH:	.XX ±1.00 .XXX ±.500 SURFAC	√)T: 3/23/22	SIZE	dwg C-A	. NO. . NT-2.4-MS .	A-TH1	REV A
NATURAL PASSIVATED	ENGR: DASARATHAN	DT: 3/23/22	SCALE	: 4:1	DO NOT SCALE	DRAWING	SHEET 1 OF 2