



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	07JAN2019	RS	HD



TUBING DIMENSIONS METRIC

Size	As Supplied (mm)		As Recovered (mm)	
	Inside Diameter	Wall Thickness	Inside Diameter	Wall Thickness
	nominal	maximum	maximum	minimum
	D	W1	d	W2
0.6	0.95 ± 0.25	0.1	0.3	0.25
0.8	1.2 ± 0.25	0.1	0.4	0.25
1.0	1.4 ± 0.25	0.1	0.5	0.25
1.5	1.9 ± 0.25	0.1	0.75	0.25
2.0	2.3 ± 0.25	0.1	1.0	0.26
2.5	2.8 ± 0.25	0.15	1.25	0.28
3.0	3.3 ± 0.25	0.15	1.5	0.28
3.5	3.8 ± 0.25	0.15	1.75	0.28
4.0	4.4 ± 0.25	0.15	2.0	0.28
6.0	6.5 ± 0.4	0.15	3.0	0.33
8.0	8.5 ± 0.4	0.15	4.0	0.33
9.0	9.5 ± 0.4	0.15	4.5	0.33
10.0	10.5 ± 0.5	0.15	5.0	0.33
12.0	12.9 ± 0.5	0.15	6.0	0.33
18.0	19.2 ± 0.6	0.2	9.0	0.46
25.0	26.4 ± 1.0	0.2	12.5	0.46

MATERIAL: SWFR X4 is a 125°C, 300 volt, VW-1 rated, UL recognized and CSA certified tubing meeting the requirements of UL 224. It is fabricated from Zerohal flame-retarded crosslinked modified flexible polyolefin.

COLOR: Black

DIMENSIONS: mm		DWN RS	07JAN2019	MATERIAL	-	FINISH	-			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK HD	07JAN2019	 TE Connectivity NAME SWFR X4 BLACK SINGLE WALL HEAT SHRINKABLE TUBING						
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES		APVD HD	07JAN2019							
PRODUCT SPEC		APPLICATION SPEC				SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
						A4		C- SWFR_X4_BLACK		
WEIGHT		CUSTOMER DRAWING				SCALE	NTS	SHEET	1 OF 1	REV A
