

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL DRAWN	13SEP2019	RV	JR

CAPABLE

- Handles up to 1000 A/1000 V

HERMETICALLY SEALED

- Suitable for application in harsh and explosive environments
- No contact oxidation over periods of non-use

VERSATILE

- Bidirectional switching
- Main contacts not polarity sensitive
- Bottom or buss bar mount
- Available with SPST-NO Auxiliary Contact

EFFICIENT

- Integrated dual-coil electronic "cut-throat" economizer with internal suppression

SPACE AND WEIGHT SAVINGS

- One of the smallest 1000 A/1000 V hermetically-sealed contactors in the industry

APPLICATIONS

- Energy Storage/Battery Storage
- Power Distribution
- Alternative Energy
- Electric Vehicles (Military and Commercial)
- Test Equipment

Specifications

ELECTRICAL

Main Contacts

- **Contact Arrangement:** SPST-NO (Form X)
- **Voltage Rating (Max.):** 1000 VDC
- **Current Rating, Continuous:** 1000 A (At 25°C ambient with four 4/0 conductors or equivalent)
- **Current Rating, Short Term:** 1200 A/180 sec
- **Contact Resistance:** 0.2 mΩ max. at rated current
- **Hot-Switching Performance, Resistive Load:**
  - 50 A/1000 VDC: 25,000 cycles
  - 130 A/1000 VDC: 10,000 cycles
  - 200 A/1000 VDC: 3500 cycles
  - 100 A/600 VDC: 10,000 cycles
  - 240 A/600 VDC: 2000 cycles
  - 1000 VDC/1200 A: 4 cycles (Break Only)
- **Maximum Pulse Through Closed Contacts:** 6000 A (half cycle, 60 Hz)
- **Dielectric Withstanding Voltage over Life:**
  - Between Open Contacts: 2800 V<sub>rms</sub>
  - Contacts to Coil: 2800 V<sub>rms</sub>/4000 VDC
  - End of Life Between Open Contacts: 2200 V<sub>rms</sub>
- **Insulation Resistance over Life, Terminal to Terminal; Terminals to Coil:**
  - Beginning of Life: 100 MΩ min. @ 500 VDC
  - End of Life: 50 MΩ min. @ 500 VDC

- **Auxiliary Contact Rating 1 A / 30 Vdc**
  - Switching Life at Maximum Rating 100K cycles
  - Auxiliary Contact Resistance (maximum over life) 1 Ω
  - Minimum Load 5 VDC / 5 mA
- **Mechanical Life:** 100,000 cycles minimum

ENVIRONMENTAL/MECHANICAL

- **Shock:** 11 ms, 1/2 sine (operating), 20 g peak
- **Sine Vibration:** 20 gpeak (operating) 55 to 2000 Hz
- **Operating Temperature Range:** -40°C to +105°C
- **Weight, Nominal:** 1.02 kg
- **Sealing:** Hermetic

COIL DATA

Coil Data @ 20°C (Internal Two-Coil Economizer)

- **Coil Voltage Range:** 24 VDC nom./32 VDC max.
- **Maximum Pickup Current:** 5.5 A
- **Nominal Holding Current:** 0.33 A
- **Pickup Voltage:** 18 VDC
- **Dropout Voltage:** 10 VDC
- **Pickup Pulse (Max):** 75 ms
- **Coil Resistance ±5%:** 4.7 Ω Pickup/72 Ω Hold
- **Coil Holding Power:** 8 W
- **Main Contacts:**
  - Operate Time (Max): 50 ms
  - Operate Bounce (Typ.): 5 ms
  - Release (Typ.): 8 ms

Part Numbering System

BRAND

K KILOVAC

BASIC RATING

1K 1000 V/1000 A

SIZE

06 Size 06 (EV202 Package)

CONFIGURATION

X Form X, Normally Open

COIL VOLTAGE

- 012E 12 V Coil Economized
- 012H 12V Coil Economized w/SPST-NO Aux
- 024E 24 V Coil Economized
- 024H 24V Coil Economized w/SPST-NO Aux

COIL LEAD LENGTH

A 15-inch coil leads


CONTACT TERMINATION

- F Finned Heat Sink Bus Bar (Nickel-Plated Aluminum)
- G Flat Bus Bar (Nickel-Plated Copper)
- H 4X 1/4-20 UNC Female Threads, .187" deep. (2)

MOUNTING

A Bottom Mount

(2) User furnished bus bar must be equivalent to 4X 4/0 conductor. Torque to 45-55 in-lbs. per connection (5.1 - 6.2 NM)



As one of the smallest, lowest cost, hermetically sealed 1000 A/1000 V switching devices in the Industry, the KILOVAC K1K contactor from TE Connectivity (TE) operates reliably in harsh and explosive environments without oxidation or contamination of contacts, even after long periods of non-operation. The K1K is well suited for power switching at voltages as low as 5 VDC and as high as 1000 VDC. Typical applications include main disconnect contactor for large battery bank applications, for carry and interrupt battery fault currents and other high current applications, power/motor control circuit isolation, and circuit protection and safety.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
INCHES	
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
	ANGLES ± -

MATERIAL	FINISH
-	-

DWN	RV	13SEP2019
CHK	RV	13SEP2019
APVD	JR	13SEP2019
PRODUCT SPEC		
APPLICATION SPEC		
WEIGHT	-	
CUSTOMER DRAWING		

		TE Connectivity	
		NAME	
K1K06-SERIES		RESTRICTED TO	
SIZE	CAGE CODE	DRAWING NO	
A3	-	©-K1K06-SERIES	
SCALE		SHEET	REV
NTS		1 OF 1	A