




A	CUSTOMER DRAWING RELEASE	10/17/2023	JH	CM
REV	DESCRIPTION	DATE	DWN	APVD

THIS DRAWING IS A CONTROLLED DOCUMENT

DWG NO
RXM-FFF-KH3



1. ALL DIMENSIONS ARE IN MM [INCHES].
2. ALL MATERIALS PRODUCT AND PROCESSES MUST MEET REQUIREMENT OF TE CONNECTIVITY ENVIRONMENTAL STANDARD TEC-138-702 CONTAINS NO BANNED OR RESTRICTED SUBSTANCES.
3. NO REACH SVHC SHALL BE CONTAINED ABOVE THE TRESHOLD AS DEFINED IN REACH SVHC COMPLIANCE DEFINITION IN ANNEX "A" OF TEC-138-702.
4. ELECTRICAL DATA SHOWN FOR REFERENCE ONLY. SEE DATA SHEET FOR COMPLETE PROGRAMMING, ASSIGNMENT, INTEGRATION AND PROCESSING DETAILS MARKING PERMINANT USING KAPTON HIGH TEMPERATURE LABELS.
 1. "FFF" SHALL INDICATE FREQUENCY OF MODULE PROGRAMMING.
6. REFLOW CAPABLE. SEE SHEET 2 FOR PROCESSING DETAILS
7. PRODUCT PROTECTED DURING SHIPMENT USING TUBES OF 20PC SHIPPED IN 260PC CARTON.




PART NUMBER	FREQUENCY
RXM-315-KH3	315MHz
RXM-418-KH3	418MHz
RXM-433-KH3	433MHz

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	JHAGER	10/17/23	 KH3 TYPE RECIEVER MODULE MODULE TAB FREQ.			
		CHK	-	-				
		APVD	CMURPHY	10/17/23				
		PRODUCT SPEC	-	-				
		APPLICATION SPEC	-	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT	g		A3	00779	Ⓒ-RXM-FFF-KH3	-
CUSTOMER DRAWING					SCALE	5:1	SHEET	1 OF 2
					REV	A		

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ± 0.5
	1 PLC ± 0.25
	2 PLC ± 0.13
	3 PLC
	4 PLC
	ANGLES ± 30'
MATERIAL	FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT DWG NO RXM-FFF-KH3



RECOMMENDED PCB LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JHAGER 10/17/23					
DIMENSIONS: mm		CHK -					
		APVD CMURPHY 10/17/23	KH3 TYPE RECIEVER MODULE MODULE TAB FREQ.				
		PRODUCT SPEC -					
MATERIAL		APPLICATION SPEC -	SIZE A3	CAGE CODE 00779	DRAWING NO ©-RXM-FFF-KH3	RESTRICTED TO -	
FINISH		WEIGHT g	CUSTOMER DRAWING		SCALE 5:1	SHEET 2 OF 2	REV A