
CGAT (Black)

Dual Wall tube. Commercial grade flame retarded heat shrink tubing with an adhesive. To be used for insulation, protection and environmental sealing of cable and similar substrates.



PRODUCT DIMENSIONS

SIZE	Inside Diameter as supplied (min) mm (inch) D	Inside Diameter after recovery (max) mm (inch) d	Wall Thickness after recovery (nom) mm (inch) W	Wall Thickness Tolerance after recovery mm (inch)
3/1	3.0 (.118)	1.0 (.039)	1.00 (.039)	0.25 (.010)
6/2	6.0 (.236)	2.0 (.079)	1.00 <i>(.039)</i>	0.25 (.010)
9/3	9.0 <i>(.354)</i>	3.0 (.118)	1.35 (.053)	0.25 (.010)
12/4	12.0 <i>(.472)</i>	4.0 (.157)	1.50 <i>(.059)</i>	0.25 (.010)
18/6	18.0 <i>(.709)</i>	6.0 (.236)	1.70 <i>(.067)</i>	0.25 (.010)
24/8	24.0 <i>(.945)</i>	8.0 (.315)	1.90 (.075)	0.25 (.010)
39/13	39.0 <i>(1.535)</i>	13.0 (.512)	2.10 (.083)	0.25 (.010)

CGAT STANDARD SIZE REFERENCE DIMENSIONAL DRAWING							
			©2020		TE Connectivity Ltd. family of companies All Rights Reserved		
				DIMENSIONS IN	TITLE		
				mm (Inch)	CGAT - IRR	ADIATED MODIFIED POL	YOI FFIN
				\bigoplus	DUAL WALL HEAT SHRINK TUBING		
A	Initial Release	HD	12/07/2021	SHEET	NO		REV
REV	ENGINEERING CHANGE	CHK	DATE	1 of 2	CGAT (B	lack) – Standard sizes	Α
NEV	LINGINLLKING CHANGE	CITK	DATE		,	,	-

CGAT (Black)

PRODUCT INFORMATION

General use dual wall polyofelin with meltable adhesive liner Shrink Ratio – 3:1 Longitudinal Shrinkage on full recovery 0 to -15% Material conforms to TE Specification RW-2050 Colour: Black Flame Retardant

Tubing cut to specific lengths can be supplied from the product sizes referenced within this drawing.

Cut length tolerances are as per the following table:

STANDARD CUTTING TOLERANCES (mm)				
CUT LENGTH	TOLERANCE			
Up to 9.9mm	±0.5mm			
10mm to 24.9mm	±1.0mm			
25mm to 54.9mm	±1.5mm			
55mm to 99.9mm	±3.0mm			
100mm to 149.9mm	±4.0mm			
150mm to 499.9mm	±5.0mm			
500mm to 1200mm	±12.5mm			



SHEET