
REVISION				
REV	DESCRIPTION	DATE		
F	REVISED PER ECO-18-008206	29MAY2018		



Notes:

- 1. Application: Electroless Nickel MTC SH1 Receptacle Shells
- 2. For Use With MIL—C 39029/58—360, Size 22 Contacts
- 3.\ End Cap: Glass Filled Nylon, Flame Retardant, Black
 - Main Body: Aluminum, Electroless Nickel Plated
 - Screws: 4—40 Phillips Head, Stainless Steel 302, Passivated, Captive, Self—Locking. Alternative material A—286
- 6. Electrical Contacts: Brass / Beryllium Copper, Gold Plated
- 7. Markings: High Contrast Ink
- 8. Bus Bar, Beryllium Copper, Electroless Nickel Plated
- 9. Meets Raychem Specification C-6114 Requirements
- 10. Contact Cavity Bore Dia, Plated: .0685/0690 (REF)

© 2004 TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

		SPECIFICATION	CONTROL DRAWING
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE INCHES. METRIC DIMENSIONS ARE IN BRACKETS.	T RATZLAFF 26MAR2004		CTRONICS STITUTION DRIVE ARK, CA 94025 Raychem
DECIMAL TOLERANCES .XXX ± 0.005 [0.13 mm] .XX ± 0.010 [0.25 mm] .X ± 0.020 [0.50 mm]	SEE NOTES	1-INCH MTC GROUNDING BLOCK WITHOUT FINGERS	
ANGLE TOLERANCE .X ± 0.5 DEG.	SEE NOTES		
WEIGHT (NOM) LBS. 0.0126 [5.7 gm]	THIRD ANGLE PROJECTION	SIZE CAGE CODE DWG. NO.	CHA-0305
C041087.DWG	TINOULOTION	DO NOT SCALE THIS DRAWING	SHEET 1 OF 1