

P	LTR	DESCRIPTION	DATE	DWN	APVD
A		INITIAL DRAWN	09AUG2019	RV	DH

Ordering Information

SRC | **7** | **2** | **A** | **C** | **C** | **A**


Series SRC
Repeat Cycle Timer.

Output
2 = DPDT Relay

Timing Range Off-Time
A = 0.1 to 3 sec.
B = 0.5 to 15 sec.
C = 1 to 30 sec.
D = 2 to 60 sec.
E = 4 to 120 sec.
F = 6 to 180 sec.
G = 10 to 300 sec.
I = 2 to 60 min.
K = 3 to 180 cycles
L = 0.33 to 10 min.
M = 0.5 to 15 min.
N = 1 to 30 min.
P = 0.1 to 10 sec.

Timing Range On-Time
A = 0.1 to 3 sec.
B = 0.5 to 15 sec.
C = 1 to 30 sec.
D = 2 to 60 sec.
E = 4 to 120 sec.
F = 6 to 180 sec.
G = 10 to 300 sec.
I = 2 to 60 min.
K = 3 to 180 cycles
L = 0.33 to 10 min.
M = 0.5 to 15 min.
N = 1 to 30 min.
P = 0.1 to 10 sec.


Timing Adjustment
A = Dual Knob Adjust



Wiring Diagram (Bottom View)

Operating Voltage

(+10%, -15%)
A = 120VAC, 50/60 Hz. / 120VDC
B = 240VAC, 50/60 Hz.
E = 24VAC, 50/60 Hz. / 24VDC
F = 48VAC, 50/60 Hz. / 48VDC
Q = 12VDC



Outline Dimensions

ALL DIMENSIONS ARE IN INCHES(MM).

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	RV	09AUG2019		TE Connectivity				
		CHK	RV	09AUG2019		NAME				
		APVD	DH	09AUG2019		SRC SERIES, TIME DELAY RELAY				
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		-				
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APPLICATION SPEC		-				
MATERIAL		FINISH		WEIGHT		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO
-		-		-		A3		-	©=SRC-SERIES	-
CUSTOMER DRAWING				SCALE		SHEET		REV		
				NTS		1 of 1		A		