




SHELL SIZE	MS CODE	A THREAD 0.1-0.3L-TS	ØB MAX	ØC MAX	ØD MAX
09	A	0,6250	21,8	12,7	17,4
11	B	0,7500	25,0	15,9	20,6
13	C	0,8750	29,4	19,1	23,8
15	D	1,0000	32,5	22,2	27,0
17	E	1,1875	35,7	25,4	30,1
19	F	1,2500	38,5	28,6	33,3
21	G	1,3750	41,7	31,8	36,5
23	H	1,5000	44,9	34,9	39,7
25	J	1,6250	48,0	38,1	42,8

PC460-26-1935SN-1-C-A

SERIES _____
 STYLE _____
 SHELL SIZE _____
 INSERT ARRANGEMENT _____
 CONTACT STYLE: P = PIN S = SOCKET _____
 ALTERNATE KEYING N,A,B,C,D,E _____
 MATERIAL _____
 PLATING _____
 RING OPTION: _____
 A - RING TO SUIT SINGLE BRAID
 B - RING TO SUIT DOUBLE BRAID
 OMIT IF NO RING REQUIRED

CODE	MATERIAL / FINISH
1-C	ALUMINIUM / ELECTROLESS NICKEL
1-B	ALUMINIUM / CADMIUM OLIVE DRAB OVER ELECTROLESS NICKEL
1-ZB	ALUMINIUM / ZINC COBALT OLIVE DRAB OVER ELECTROLESS NICKEL
1-ZK	ALUMINIUM / ZINC COBALT BLACK OVER ELECTROLESS NICKEL
1-ZN	ALUMINIUM / ZINC NICKEL BLACK PASSIVATE OVER ELECTROLESS NICKEL
4-J	STAINLESS STEEL / PASSIVATE
2-Z	NICKEL ALUMINIUM BRONZE / SHOT BLAST

LIST NOT EXHAUSTIVE, FOR COMPREHENSIVE LIST AND SPECS, SEE WEBSITE

MIL-DTL-38999 STYLE
 SHELL MATERIAL - SEE TABLE
 FINISH - SEE TABLE
 INSERT - THERMOSET PLASTIC
 SEALS - SILICONE ELASTOMER
 SUPPLIED WITH CRIMP CONTACTS

COPY FILED WITH CHINA CONTRACTS																			
DRAWN	M. PAUL	DATE	08/04/2013		3RD ANGLE PROJECTION NOT TO SCALE	PART NUMBER:			PC460-26-xxxxxx-x-x			 Polamco 							
SALES APPR	JC	DATE	08/04/2013			TITLE:			PLUG WITH INTEGRAL BACKSHELL										
DESIGN APPR				UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0.25MM ANGULAR +/- 1°			ASSY USED ON: D38999/26												
PROD APPR																			
QUAL APPR				MATERIAL SEE PART NUMBER BREAKDOWN			THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.			POLAMCO LTD, WESTON LOCK, LOWER BRISTOL ROAD BATH BA2 1EP			SHT 1			DRAWING NO: C3504			
ISSUE	REV.	DCR																	
1		---		FINISH SEE PART NUMBER BREAKDOWN															
NCAGE CODE U5792				WEIGHT		---													