




TOUS DROITS RESERVES


BSMB-35/150	E05256N001	BLOCKED
DESCRIPTION	TCPN	TYPE



BSMU-35/150	A84872N001	UNBLOCKED
DESCRIPTION	TCPN	TYPE



REVISIONS					
P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
	O	CREATION	09JUN2004	NA	AD
	A	CHAMFER UPDATE	09JUL2004	NA	AD
	B	UPDATE TABLE WITH CU FLEX CABLE	20JUN2019	BM	NA



		AL				CU			
		RM ROUND STRANDED	RE ROUND SOLID	SM SECTOR STRANDED	SM SECTOR SOLID	RM ROUND STRANDED	RE ROUND SOLID	SM SECTOR STRANDED	ROUND FLEXIBLE
CONDUCTOR CROSS-SECTION QUERSCHNITTSBEREICH	mm ²	35 - 150	35 - 150	50 - 95 (120-150 with rounding)	50 - 120	35 - 150	35 - 50	50 - 95	50-70
	II	#2 compact to 250 kcmil standard				#2 compact to 250 kcmil standard			
CONDUCTOR DIAMETER LEITERDURCHMESSER	mm ²	Ø 6.8 - Ø 15	Ø 6.5 - Ø 14	-	-	Ø 6.6 - Ø 15	Ø 6.5 - Ø 8	-	Ø 9 - Ø 13.1
	II	.262" to .575"				.262" to .575"			

TOLERANCES UNLESS OTHERWISE SPECIFIED
TOLERANCES NON SPECIFIEES: -

THIS DRAWING IS A CONTROLLED DOCUMENT.
CE PLAN EST UN DOCUMENT CONTROLE PAR TYCO ELECTRONICS CORPORATION
IL EST SUSCEPTIBLE D'ETRE REVISE. CONTACTER LE SERVICE
TECHNIQUE POUR OBTENIR LA DERNIERE REVISION.

DIMENSIONS:
mm

MATERIAL
MATIERE

AL ALLOY
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:
TOLERANCES NON SPECIFIEES (SUIV NB DE DECIMALES):
0 PLC/DEC: ±0
1 PLC/DEC: ±0
2 PLC/DEC: ±0
3 PLC/DEC: ±0
4 PLC/DEC: ±0
ANGLES ±°

FINISH
FINITION

TINNED
-

DWN/DESSINE
N. ALMEIDA
09JUN2004

CHK/VERIFIE
R. BUTHIOT
-

APVD /APPROUVE
A. DUPONT
-

PRODUCT SPEC
SPEC. PRODUIT
-

APPLICATION SPEC
SPEC. APPLICATION
-

WEIGHT
MASSE APPROX. 100 g

CUSTOMER DRAWING /PLAN CLIENT

NAME
TITRE

BSMU-35/150
BSMB-35/150
-

SIZE
FORMAT A3

CAGE CODE
00779

DRAWING NO
No PLAN C-1756559

RESTRICTED TO
RESERVE A -

UNIQUEMENT
POUR REFERENCE

SCALE
ECHELLE 2:1

SHEET
FEUILLE 1

OF
DE 1

REV
B

1470-19 (3/13)