
CUSTOMER DRAWING



Product	Pro	oduct Dimensio	ons	Cable Dimensions			
Name	L	øA	øB	øD	øE	øE	
	max	min	min	max	min	max	
D-607-20	23.0	5.20	4.7	4.7	2.4	3.3	
	(0.900)	(0.204)	(0.185)	(0.185)	(0.095)	(0.130)	

MATERIALS

- 1. INSULATION SLEEVE: Heat-shrinkable, transparent blue, radiation cross-linked polyvinylidene fluoride.
- 2. SOLDER PREFORM WITH FLUX:
 - SOLDER: TYPE Sn63 per ANSI-J-STD-006.
- FLUX: TYPE ROL0 per ANSI-J-STD-004.
- 3. TERMINATOR BODY: Base metal: Copper alloy.

Plating: Tin/Lead solder.


APPLICATION

1. This part is designed for use in attaching a shielded or coaxial cable to a PCB.

2. Install using TE Connectivity-approved convection or infrared tools in accordance with Raychem assembly procedure ES-61139.

3. Temperature range: -55°C to +150°C.

For best results, prepare the cable as shown:



TE Connectivity, TE connectivity (logo), Raychem, Thermofit, and SolderSleeve are trademarks

= <u>TE</u>	<i>Raychem</i> THERMOFIT DEVICES			TITLE: SOLDERSLEEVE PCB TERMINATOR					
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCHES DIMENSIONS ARE BETWEEN BRACKETS.					DOCUMENT NO.: D-607-20				
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	ANGLES: ROUGHNI MICRON	this drawing at any time. Users should NESS IN evaluate the suitability of the product for		Revision: 4		Issue Date: March 2020			
DRAWN BY: DATE: M. FORONDA 28-0		E: 28-Oct-98	ECO: ECO-20-003572		SCALE: None	SIZE: A	SHEET: 1 of 1		

Print Date: 17-Mar-20 If this document is printed it becomes uncontrolled. Check for the latest revision.