


NOTE:-

1. BATCH No. & PART No., BREAKDOWN.



SHELL SIZE	A REF	B ±0.20	C +0.1/-0.0	phi D +0.0/-0.13	E +0.15/-0.0	F ±0.10	phi G MAX	phi H ±0.10	L MAX
8	16.50	21.40	3.2	12.00	17.21	15.98	11.10	14.50	27.20
10	19.50	25.90	3.2	15.00	17.21	15.98	14.27	17.40	32.00
12	24.00	29.10	3.2	19.05	17.21	15.98	17.44	21.90	35.20
14	27.00	32.50	3.2	22.22	17.21	15.98	20.60	25.00	38.40
16	30.30	34.80	3.2	25.40	17.21	15.98	23.77	28.20	41.00
18	33.70	38.20	3.2	28.57	17.21	15.98	26.94	31.40	44.70
20	37.00	41.60	3.2	31.75	17.21	15.22	30.11	34.60	47.90
22	40.00	44.95	3.2	34.90	17.21	15.22	33.29	37.75	51.10
24	43.30	49.35	3.2	38.10	17.21	15.22	36.46	40.90	55.80

CONTACT SIZE	phi X MAX	phi Y MAX
22	0.72	1.25
20	0.72	1.25
16	1.57	2.61

ISSUE	CHANGE NOTE	DRAWN	CHECKED	APP. ENG.	DATE	APP. IED.
C	60006	ADH	NDL	NDL	04.04.11	
B	53804	NDL	JAK	JAK	14.02.07	
A	036167	JV	MW	IKG	30.09.98	

MATERIAL

HEAT TREATMENT & FINISH

© THE COPYRIGHT OF THIS DRAWING IS RESERVED BY DEUTSCH LTD. IT IS ISSUED ON CONDITION THAT IT IS NOT COPIED, REPRODUCED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE CONSENT IN WRITING OF DEUTSCH LTD.

GENERAL TOLERANCES UNLESS OTHERWISE STATED.

±0.4mm ON WHOLE NUMBERS  
±0.2mm ON ONE PLACE DECIMALS  
±0.1mm ON TWO PLACE DECIMALS  
±1/2° ON ANGLES  
±0.05mm ON DRILLED HOLES

REMOVE ALL BURRS AND SHARP EDGES 0.1 MAX. UNLESS OTHERWISE STATED.



DEUTSCH LTD

EAST GRINSTEAD, WEST SUSSEX, RH19 1RW TEL:- (01342) 410033

TITLE PCB BOX MOUNTING RECEPTACLE AS TYPE 2

DRAWING NUMBER

603592  
ENVELOPE DRG.,

SCALE

2:1

DIMS. IN MILLIMETRES