
CGPT (3:1 Ratio)

Single Wall tube. A Commercial grade heat shrink tube primarily used for electrical insulation. Has a UL224 approval. Available in several colours.



PRODUCT DIMENSIONS

SIZE	Inside Diameter as supplied (min) mm (inch) D	Inside Diameter after recovery (max) mm (inch) d	Wall Thickness after recovery (nom) mm (inch) W	Wall Thickness Tolerance after recovery mm (inch)
1.5/0.5	1.5 <i>(.059)</i>	0.5 (.020)	0.45 (.018)	0.12 (.005)
3/1	3.0 (.118)	1.0 (.039)	0.55 <i>(.022)</i>	0.12 <i>(.005)</i>
6/2	6.0 <i>(.236)</i>	2.0 (.079)	0.65 <i>(.026)</i>	0.12 (.005)
9/3	9.0 <i>(.354)</i>	3.0 (.118)	0.75 (.030)	0.15 <i>(.006)</i>
12/4	12.0 <i>(.472)</i>	4.0 <i>(.157)</i>	0.75 (.030)	0.15 <i>(.006)</i>
18/6	18.0 <i>(.709)</i>	6.0 <i>(.236)</i>	0.85 <i>(.033)</i>	0.15 <i>(.006)</i>
24/8	24.0 <i>(.945)</i>	8.0 (.315)	1.00 (.039)	0.20 <i>(.008)</i>
39/13	39/13 39.0 (1.535) 13.0 (.512		1.15 (.045)	0.25 (.010)

CGPT (3:1 Ratio) – STANDARD SIZE REFERENCE DIMENSIONAL DRAWING			©2020		TE Connectivity Ltd. family of companies All Rights Reserved		
				DIMENSIONS IN mm (Inch)	CGPT (3:1 I POLYOLEF	Ratio) – IRRADIATED M IN SINGLE WALL HEAT TUBING	ODIFIED SHRINK
Α	Initial Revision	HD	20/04/2021	SHEET	NO		REV
REV	ENGINEERING CHANGE	CHK	DATE	1 of 2	CGPT (3:1 F	Ratio) – Standard Sizes	Α

CGPT (3:1 Ratio)

PRODUCT INFORMATION

General use single wall Polyolefin Tubing. Shrink Ratio - 3:1 Longitudinal Shrinkage on full recovery – 0 to -10% Material conforms to TE Specification 108-120044 Standard Colours: Black, White, Red, Blue, Yellow, Clear Non-Standard Colours: Brown, Orange, Green, Violet, Grey Flame Retardant (Colours only)

Tubing cut to specific lengths can be supplied from the product sizes referenced within this drawing.

Cut length tolerances are as per the following table:

STANDARD CUTTING TOLERANCES (mm)				
CUT LENGTH	TOLERANCE			
Up to 9.9mm	±0.5mm			
10mm to 24.9mm	±1.0mm			
25mm to 54.9mm	±1.5mm			
55mm to 99.9mm	±3.0mm			
100mm to 149.9mm	±4.0mm			
150mm to 499.9mm	±5.0mm			
500mm to 1200mm	±12.5mm			

