







NOTE:-

1. BATCH No. & PART No., BREAKDOWN.

DEUTSCH AS2 ** - ** P/S * - 978M RP654321

SERIES _____ BATCH No.
SHELL STYLE _____ MODIFICATION CODE
ARRANGEMENT _____ KEYWAY ORIENTATION
P=PIN OR S=SOCKET

2. THIS CONNECTOR MAY ONLY BE MOUNTED WITH PANEL IN FRONT OF FLANGE.

SHELL SIZE	A REF	B ±0.20	C THREAD	øD +0.0/-0.13	E +0.15/-0.0	F +0.0/-0.13	øG MAX	øH ±0.10	L MAX
8	18.00	21.40	M3x0.5	12.00	17.21	16.05	11.10	14.50	29.00
10	19.00	25.90	M3x0.5	15.00	17.21	16.05	14.27	17.40	33.55
12	23.00	29.10	M3x0.5	19.05	17.21	16.05	17.44	21.90	36.85
14	26.00	32.50	M3x0.5	22.22	17.21	16.05	20.60	25.00	40.05
16	31.80	34.80	M3x0.5	25.40	17.21	16.05	23.77	28.20	42.65
18	35.20	38.20	M3x0.5	28.57	17.21	16.05	26.94	31.40	45.70
20	38.50	41.60	M3x0.5	31.75	17.21	15.29	30.11	34.60	49.20
22	42.00	44.95	M3x0.5	34.90	17.21	15.29	33.29	37.75	52.60
24	44.80	49.35	M3x0.5	38.10	17.21	15.29	36.46	40.90	57.00

CONTACT SIZE	øX MAX	øY MAX
22	0.72	1.25
20	0.72	1.25
16	1.57	2.61

ISSUE	CHANGE NOTE	DRAWN	CHECKED	APP. ENG.	DATE	APP. MARKT.	I.GOULDING
B	57206	NDL	ADH	JAK	28.05.09		
A	56858	NDL	ADH	JAK	05.03.09		

MATERIAL

HEAT TREATMENT & FINISH

© THE COPYRIGHT OF THIS DRAWING IS RESERVED BY DEUTSCH LTD. IT IS ISSUED ON CONDITION THAT IT IS NOT COPIED, REPRODUCED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE CONSENT IN WRITING OF DEUTSCH LTD.

GENERAL TOLERANCES UNLESS OTHERWISE STATED.

±0.4mm ON WHOLE NUMBERS
±0.2mm ON ONE PLACE DECIMALS
±0.1mm ON TWO PLACE DECIMALS
±1/2° ON ANGLES
±0.05mm ON DRILLED HOLES

REMOVE ALL BURRS AND SHARP EDGES 0.1 MAX. UNLESS OTHERWISE STATED.

DEUTSCH
LTD

EAST GRINSTEAD, WEST SUSSEX, RH19 1RW TEL:- (01342) 410033

TITLE AS TYPE 2 RECEPT.
PCB BOX MNT. THREADED
CLINCH NUTS. MOD 978M.
ENVELOPE DETAILS

DRAWING NUMBER

610951-ENV