





THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES (TE). IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN TE PERSONNEL WITHOUT AUTHORIZATION FROM TE (www.te.com).

DRAWING NUMBER:
611183-ENV



DATE CODE AND PART NUMBER

RED COLOUR BAND



NOTES:

1. PART NUMBER BREAKDOWN EXAMPLE:

H***D W3 1 4 T W ** ** S N ***
DATE CODE
WILDCAT SERIES 3
REAR ACCESSORY
(1 = REAR BOOT / BRAID)
SHELL TYPE
TRI-START THREADS
SHELL SIZE
OPTION CODE (IF REQUIRED)
KEY ORIENTATION
CONTACT TYPE P=PIN, S=SOCKET
PLANFORM (SEE TABLE)
FINISH
(SEE FINISH TABLE FOR OPTIONS)

2. CONNECTOR MEETS THE REQUIREMENTS OF MIL-DTL-38999 SERIES 3.

SHELL SIZE & PLANFORM	ØA MAX	ØB MAX	C MAX	D MAX	ØE ±0.10	F ±0.10
09-11	11.14	30.31	27.11	23.10	17.80	16.89
11-23	14.31	35.01	31.91	26.20	20.98	19.43
13-41	17.49	38.21	35.01	31.86	25.68	24.16
15-64	20.66	41.41	38.21	35.87	28.90	27.43

LIST OF FINISH OPTIONS	
CLASS CODE	FINISH
W	ALUMINIUM WITH OLIVE DRAB CADMIUM
F	ALUMINIUM WITH ELECTROLESS NICKEL
Z	ALUMINIUM WITH ZINC NICKEL
S	STAINLESS STEEL WITH NICKEL
K	STAINLESS STEEL PASSIVATED
B	ALUMINIUM BRONZE
G	SPACE GRADE

AA	DUK-71751	NDL	KSC	KJF	CEO	06/07/2020
ISSUE	CHANGE NOTE	DRAWN	CHECKED	APP. ENG.	APP. MARKETING	DATE

BS8888 THIRD ANGLE PROJECTION 	MATERIAL: -----		FINISH: SEE TABLE	 DEUTSCH TE CONNECTIVITY UK LTD., ST. LEONARDS-ON-SEA, TN38 9RF, UK.	
UNLESS OTHERWISE STATED: DIMENSIONS: mm [INCHES]	TITLE: WILDCAT JAM NUT RECEPT. W314. ENVELOPE DETAILS. TYPE: CUSTOMER DRAWING				
IF IN DOUBT, ASK	SIZE: A3	SCALE: 2:1	DRAWING NUMBER: 611183-ENV		SHEET: 1 OF 1 ISSUE: AA