

SPECIFICATION CONTROL DRAWING

CMC-0554

Title WIRE, ELECTRIC, RADIATION-CROSSLINKED, MODIFIED
ETFE-INSULATED, NICKEL-COATED COPPER


Date 9-29-98

Revision G

This specification sheet forms a part of the latest issue of Raychem Specification 80.

CONDUCTOR - NICKEL-COATED COPPER

JACKET - RADIATION-CROSSLINKED,
MODIFIED, FLEXIBLE ETFE



PRIMARY INSULATION - RADIATION-CROSSLINKED,
MODIFIED, FLEXIBLE ETFE
COLOR - LIGHT GREEN

BRAID - NOMEX BRAID TREATED
TO PREVENT FRAYING

W & C DESIGN
RED STAMP - CONTROL COPY
BLACK STAMP - CHECK FOR
LATEST ISSUE

TABLE I. CONSTRUCTION DETAILS

PART NUMBER	WIRE SIZE (AWG)	CONDUCTOR STRANDING (number x AWG)	DIAMETER OF STRANDED CONDUCTOR (in.)		FINISHED WIRE		
			MINIMUM	MAXIMUM	MAXIMUM RESISTANCE AT 20°C (ohms/1000 ft.)	DIAMETER (in.)	MAXIMUM WEIGHT (lbs/1000 ft.)
CMC-0554-10-*	10	37 x 28	.106	.113	1.24	.106 ± .006	38.2
CMC-0554- 8-*	8	133 x 29	.158	.173	.694	.231 ± .008	73.8
CMC-0554- 6-*	6	133 x 27	.198	.217	.436	.282 ± .010	111.
CMC-0554- 4-*	4	133 x 25	.250	.274	.275	.340 ± .010	175.
CMC-0554- 2-*	2	665 x 30	.320	.340	.177	.422 ± .016	267.
CMC-0554- 0-*	0	1045 x 30	.395	.425	.113	.519 ± .016	436.
CMC-0554- 00-*	00	1330 x 30	.440	.475	.089	.569 ± .016	538.
CMC-0554-000-*	000	1665 x 30	.500	.540	.071	.645 ± .016	642.

TABLE II. PERFORMANCE DETAILS

PART NUMBER	BEND TESTING	
	MANDREL DIAMETER (in.) (±3%)	WEIGHT (lb) (±3%)
	CROSSLINKING PROOF TEST	CROSSLINKING PROOF TEST
CMC-0554-10-*	2.00	3.00
CMC-0554- 8-*	3.00	4.00
CMC-0554- 6-*	4.00	4.00
CMC-0554- 4-*	5.00	4.00
CMC-0554- 2-*	6.00	6.00
CMC-0554- 0-*	8.00	6.00
CMC-0554- 00-*	10.0	6.00
CMC-0554-000-*	10.0	8.00

COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-881.

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.

Page 1 of 2

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.

Raychem

Raychem Corporation
300 Constitution Drive, Menlo Park, California 94025
1-800-2 Raychem Fax: 1-650-361-6297

WIRE RATINGS AND ADDITIONAL REQUIREMENTS**W & C DESIGN**

RED STAMP - CONTROL COPY

BLACK STAMP - CHECK FOR

LATEST ISSUE

TEMPERATURE RATING: 200°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms)

COLOR: White, or dark green with Munsell color limits 5Y 3/2 and 5B 2/0.5

CONCENTRICITY: 70% (minimum)**+ CROSSLINKING PROOF TEST: 300 ± 3°C for 7 hours****INSULATION ELONGATION AND TENSILE STRENGTH:**

(Both layers - pulled individually or together)

Elongation, 150% (minimum)

Tensile Strength, 3000 lbf/in² (minimum)**INSULATION FLAWS:**

Primary Insulation,

Impulse Dielectric Test, 8.0 kV (peak)

Finished Wire,

Impulse Dielectric Test, 8.0 kV (peak)

INSULATION THICKNESS:

For AWG 2 and larger: 0.010 in. (minimum) for primary insulation

0.015 in. (minimum) for outer jacket

For AWG 8-4: 0.008 in. (minimum) for primary insulation

0.012 in. (minimum) for outer jacket

For AWG 10: 0.005 in. (minimum) for primary insulation

0.005 in. (minimum) for outer jacket

SHRINKAGE: 200 ± 3°C for 6 hours, 0.250 in. (maximum) in 12 in.**VOLTAGE WITHSTAND TEST (POST ENVIRONMENTAL): 2500 volts (rms), 60 Hz****+ Test performed prior to application of braid.****PART NUMBER:**

The *** in the part numbers on page 1 shall be replaced by color code designators, except that green shall be dark green and the designator shall be 5D.

Example: *AWG 2, white: CMC-0554-2-9

AWG 2, dark green: CMC-0554-2-5D

PRODUCT IDENTIFICATION: Mark outer braid in a contrasting color at 12 inch (nominal) intervals with the following: "CMC-0554-AWG-06090"