




DRAWING NUMBER

611746-ENV

A3

BS 8888
THIRD ANGLE PROJECTION
IF IN DOUBT, ASK



NOTES

1. PART No. BREAKDOWN EXAMPLE:- DEUTSCH ASHD624-34220SN-025

SERIES PREFIX _____
SHELL STYLE _____
SHELL SIZE _____

POWER CONTACT CRIMP BUCKET SIZE _____
SHELL KEYING: N, A, B, C, D or E _____
CONTACT TYPE: P=PIN, S=SOCKET _____

INSERT ARRANGEMENT - 3 x SIZE 4 CONTACTS
- 2 x SIZE 20 CONTACTS

| KEY ORIENTATION | | | | | |
|-----------------|----|----|-----|-----|----|
| B° ± 1° | A | B | C | D | N |
| | 80 | 69 | 121 | 110 | 95 |

2. CONTACT CAVITY IDENTIFICATION, PIN CLOCKWISE, SOCKET ANTI-CLOCKWISE.

| | | | | | | | | | | | | | | | | | | | | | |
|-------|-------------|-------|---------|-----------|----------------|----------|--|--|--|---|--|--|---|--|--|--|--|--|--|--|--|
| | | | | | | | INITIAL PRODUCTION APPROVAL DEPT. APPROVED DATE I.E.D. MANF. PLATING DERIVED FROM: | | | MATERIAL ----- HEAT TREATMENT & FINISH ----- PACKAGING ----- SCALE 2:1 | | | GENERAL TOLERANCES UNLESS OTHERWISE STATED. ±0.4mm ON WHOLE NUMBERS ±0.2mm ON ONE PLACE DECIMALS ±0.1mm ON TWO PLACE DECIMALS ±1/2° ON ANGLES ±0.05mm ON DRILLED HOLES ALL DIAMETERS $\text{H}9/k9$ REMOVE ALL BURRS AND SHARP EDGES 0.1 MAX. UNLESS OTHERWISE STATED. DIMENSIONS IN MILLIMETRES UNLESS OTHERWISE STATED. | | | © THE COPYRIGHT OF THIS DRAWING IS RESERVED BY DEUTSCH UK. IT IS ISSUED ON CONDITION THAT IT IS NOT COPIED, REPRODUCED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE CONSENT IN WRITING OF DEUTSCH UK. TITLE ASHD PLUG ASSY 34220 PLANFORM ENVELOPE DETAILS | | | DEUTSCH ST LEONARDS ON SEA, EAST SUSSEX, TN38 9RF TEL. +44 (0)1424 852721 DRAWING NUMBER 611746-ENV | | |
| A | 62776 | NDL | BJJ | KJF | PW | 31/07/13 | | | | | | | | | | | | | | | |
| ISSUE | CHANGE NOTE | DRAWN | CHECKED | APP. ENG. | APP. MARKETING | DATE | | | | | | | | | | | | | | | |