




CTJ420E012

REVISIONS

SYM	DESCRIPTION	DATE	APPROVED
N/C	NEW RELEASE PER E.O 84352	8-10-77	<i>[Signature]</i>
A	REVISED PER E.O. 83217	10/21/77	JJM
B	REVISED PER E.O. 89017	3-20-80	L. Stalle

RESISTOR
RNC55H1002BP
TYP 5 PLACES



9. TEMPERATURE RANGE: -67°F TO 257°F (-55°C TO 125°C)
8. RESISTOR: RNC55H1002BP
WATTS: 1/10W MAX VOLTAGE: 250V
RESISTANCE VALUE: 10K Ω ±.1%
7. MATERIALS & FINISHES:
HOUSING - THERMO PLASTIC
GROMMET - SILICONE ELASTOMER
PIN CONTACTS - COPPER ALLOY PLATED GOLD
6. REQUIRES CONTACT TOOL NO. MI5570-20.
5. SEE ENVELOPE DRAWING NO. CTJ-3*-** FOR SUITABLE RAIL ASSYS.
4. FOR CONTACT DATA SEE ENVELOPE DRAWING 1625-1-0000.
3. CTJ420E 012
- CIRCUIT ARRANGEMENT.
2. THE CIRCUIT IDENTIFICATION WILL BE SCREENED ON MODULE.
1. DIMENSIONS ARE IN INCHES, UNLESS OTHERWISE SPECIFIED.

NOTE:

SIGNATURE & DATE	
DR	<i>[Signature]</i> 8-10-77
CHK	<i>[Signature]</i> 9/17/77
PE	<i>[Signature]</i> 8-15-77
APPD	
SCALE	NONE WT

MODULE ASSEMBLY,
ELECTRONIC COMPONENT
SIZE 12
SIZE 20 CONTACTS
012 ARRANGEMENT
ENVELOPE

CP	MATL CODE 16
The Deutsch Company ELECTRONIC COMPONENTS DIVISION Munich, Germany Bonn, California	
B	CTJ420E012
DWG SIZE	CODE 11129 SHEET 1 OF 1