

THIS DRAWING IS A CONTROLLED DOCUMENT
THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES (TE). IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TE PERSONNEL, WITHOUT AUTHORIZATION FROM TE (www.TE.com).

DWG NO
DMC-M_08-16_P+

USED ON
—

STANADARD MODULE

GROUNDING MODULE

CONNECTOR TYPE DMC-M

ARRANGEMENT 08-16

CONTACTS
P = Standard Male Contact
A = Without Male Contact

POLARIZATION
N, A, B, C, D

SEALING (Optional)
Omit - Standard (No Sealing)
E = Sealed 

CONNECTOR TYPE DMC-M




ARRANGEMENT 08-16

CONTACTS
P = Standard Male Contact
A = Without Male Contact



POLARIZATION
N, A, B, C, D

GROUNDING
G 

PLATING/FINISH (Optional)
Aluminium Alloy
Omit - Black Nickel
W - Olive Drab Cadmium



Polarization N (X = N)



CHARACTERISTIQUES

TEMPERATURE D'UTILISATION : -55°C a +175°C



MATERIAUX : Thermoplastique et silicone fluore

TENSION DE TENUE : 1800 V eff. ; 50 Hz

Ø SUR GAINÉ CABLES ADMISSIBLES : 1.63 a 2.77 mm

UTILISATION CONTACTS NORMALISES : MIL C 39029/58-364

 Marquages realises sur la face opposee aux clés



DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
MM			
	0 PLC	±	—
	1 PLC	±	0.05
	2 PLC	±	0.05
	3 PLC	±	0.02
	4 PLC	±	—
ANGLES ±°			
SURFACE TEXTURE			

DWN	MATERIAL		HEAT TREAT	
LAKSHMI SUDHA R	—		—	
CHK	—		—	
RAKESH S	TE Connectivity			
APVD				
VINCENT P				
NAME				
MODULE P & A				
SCALE	SIZE	DRAWING NO	SHEET	REV
3:1	A3	DMC-M_08-16_P+	1 OF 1	A