
## **CUSTOMER DRAWING**



Product Name		Product D	imensions	Cable Dimensions			
	L	A	В	K	D	Е	J±0.5
	max	min	min	min	max	min	(J±0.02)
D-142-72	17.25	2.70	3.10	150	2.70	0.9	7
	(0.680)	(0.105)	(0.125)	(5.900)	(0.105)	(0.035)	(0.275)
D-142-73	17.25	4.30	5.00	150	4.30	1.9	7
	(0.680)	(0.170)	(0.200)	(5.900)	(0.170)	(0.075)	(0.275)
D-142-74	20.5	7.00	7.70	150	7.00	3.56	7
	(0.750)	(0.275)	(0.300)	(5.900)	(0.275)	(0.140)	(0.275)

## **MATERIAL**

- 1. INSULATION SLEEVE: Heat-shrinkable, radiation cross-linked modified polyvinylidene fluoride. Transparent blue.
- 2. SOLDER PREFORM WITH FLUX:

SOLDER: TYPE Cd18 per ANSI J-STD-006.


FLUX: TYPE ROL0 per ANSI J-STD-004.

- 3. MELTABLE INSERT: Thermally stabilized thermoplastic. Color: blue.
- 4. MELTABLE INSERT: Thermally stabilized thermoplastic. Color: grey.
- GROUND LEAD: RAYCHEM 55A081-221 in accordance with MIL-W-22759/34-22 AWG 22 stranded tin plated copper. Color: white.

## **APPLICATION**

- 1. These parts are designed to provide an environment protected shield termination on cables, rated for 105°C minimum. Meeting the dimensional criteria listed, having tin or silver plated shields.
- 2. Temperature range: -55°C to +125°C.
- Install using TE Connectivity-approved convection or infrared heating tools in accordance with Raychem process standard RCPS-100-70.

For best results, prepare the cable as shown:



TE Connectivity, TE connectivity (logo), Raychem, Thermofit, and SolderSleeve are trademarks

Rayche THERMO DEVIC		OFIT	TITLE: SOLDERSLEEVE DEVICE WITH PRE-INSTALLED LEAD LOW TEMPERATURE					
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCHES DIMENSIONS ARE BETWEEN BRACKETS.					DOCUMENT NO D-142-7X			
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A		amend this draw COUGHNESS IN should evaluate		reserves the right to ring at any time. Users the suitability of the r application.	Revision: 5		Issue Date: March 2020	
DRAWN BY: DATE R. MAPALO		E: 06/15/98	ECO: ECO-2	0-003573	SCALE:: NONE	SIZE:	SHEET: 1 of 1	

Print Date: 18-Mar-20 If this document is printed it becomes uncontrolled. Check for the latest revision.