





THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES (TEC). IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TE PERSONNEL, WITHOUT AUTHORIZATION FROM TE (www.TE.com).

THIS DRAWING IS A CONTROLLED DOCUMENT

DWG NO
DMC-M_20-22_HN



CHARACTERISTIQUES

- Température d'utilisation : -55°C à +175°C
- Matériaux : Thermoplastique et silicone
- Tenue de tension : 1300 V eff. ; 50 Hz
- Masse : 3.6g Maxi (Hors contacts)
- Contacts : Femelle #22 : 724-0003-22 / EN3155003F2222 / MIL C 39029/57-354
- Outil insertion/extraction contacts : M81969/14-01

1 Marquages realises sur la face opposee aux cle

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
MM			
	0 PLC	±	0.05
	1 PLC	±	0.05
	2 PLC	±	0.05
	3 PLC	±	0.02
	4 PLC	±	0.02
ANGLES ±°			
SURFACE TEXTURE			

DWN LAKSHMI SUDHA R		MATERIAL —	HEAT TREAT —
CHK		—	—
RAKESH S		 TE Connectivity	
APVD			
VINCENT P			
NAME			
MODULE H & L			
SCALE 4:1	SIZE A3	DRAWING NO DMC-M_20-22_HN	SHEET 1 OF 1
		REV A	