
CUSTOMER DRAWING



Product Name	Color	Marking	Size Range mm ² (AWG)	L1 ±1.50 [±0.06)	L2 min	(a) min	(b) max	øB min	Wire Strip Length Nom.
D-406-0034	Yellow	DURASEAL® 24-26	0.15 - 0.25 $(26 - 24)$	31.5 [1.24]	5.0 [0.20]	3.00 [0.118]	1.40 [0.055]	1.09 [0.043]	6 to 8 (1/4 to 5/16)
D-406-0001	Red	DURASEAL® 18-22	0.5 - 1.0 (22 - 18)	31.5 [1.24]	5.0 [0.20]	3.70 [0.146]	1.40 [0.055]	1.47 [0.058]	6 to 10 (1/4 to 3/8)
D-406-0002	Blue	DURASEAL® 14-16	1.5 - 2.5 (16 - 14)	31.5 [1.24]	5.0 [0.20]	4.60 [0.181]	2.00 [0.080]	2.33 [0.092]	6 to 10 (1/4 to 3/8)
D-406-0003	Yellow	DURASEAL® 10-12	3.0 - 6.0 (12 - 10)	37.5 [1.48]	10.0 [0.39]	6.50 [0.255]	2.80 [0.110]	3.50 [0.138]	10 to 13 (3/8 to 1/2)

MATERIALS

- 1. INSULATION SLEEVE: Heat-shrinkable, radiation cross-linked polyamide (Nylon) with a polyamide-based hot-melt adhesive liner. See above table for applicable sleeve color.
- 2. CRIMP SPLICE: Tin-plated copper alloy.

BASE METAL: Copper alloy C11000 per ASTM B152. PLATING: Tin-plated per ASTM B545, Class A.

APPLICATION

- 1. These parts may be used to obtain an environment-resistant one-to-one in-line (butt) splice in wires meeting the size range and diameter restraints specified herein and having a temperature rating of not less than 85°C.
- 2. * ØA: (a) Minimum diameter as received: Wire insulation diameter must be less than this value.
 - (b) Maximum diameter after recovery: Wire insulation diameter must be larger than this value to obtain an environment resistant splice.
- 3. Wires are to be stripped per table, inserted into opposite ends of the crimp barrel, crimped with a TE Connectivity AD-1522 (22-10 AWG) or equivalent. For D-406-0034, Pro-Crimper III with die set 1976357-1 (24-26 AWG) or equivalent may be used. The sleeve must be heated along its entire length until the crimp marks are gone and the ends of the sleeve recover onto the wires.
- $4. \ Spliced \ assemblies \ will \ meet \ the \ requirements \ of \ TE \ Connectivity \ / \ Raychem \ specification \ RB-107.$
- 5. Except for D-406-0034, all of the parts covered by this drawing are UL Listed (US and CANADA), File #E87681.

-	TE 18	Connectivity	Raychem Devices	DURASEAL CRIMP SPLICE ENVIRONMENT RESISTANT				
Unless otherwise are shown in [bra	1	ions are in millimete	D-406-00XX					
TOLERANCES:	ANGLES: N/A	Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.			D 400 00	77171		
0.00 N/A	ROUGHNESS			REV.:	REV DATE: 13-Dec-2018			
0.0 N/A 0 N/A	IN MICRON			C3				
DRAWN BY:	CAGE CODE:	DRAWN DATE:	ECO No.:	SCALE:	SIZE:	SHEET:		
P. TALLY	06090	1/28/2008	ECO-18-019635	NTS	A	1 of 1		