
SPECIFICATION CONTROL DRAWING



Product Revision				Size Range	L1 ±1.5	L2	øA*		øΒ	Wire Strip	
Product Name		Color	Marking	mm ² (AWG)	$(L1 \pm 0.06)$	min	(a)	(b)	min	Length Nom.	
D-406-2007	С	Red	22 - 18 AWG	0.5 - 1.0 (22 - 18)	37.0 (1.50)	10.0 (0.39)	4.3 (0.170)	1.4 (0.055)	1.47 (0.058)	6 to 10 (1/4 to 3/8)	
D-406-2008	С	Blue	16 - 14 AWG	1.5 - 2.5 (16 - 14)	37.0 (1.50)	10.0 (0.39)	5.0 (0.197)	2.0 (0.080)	2.33 (0.092)	6 to 10 (1/4 to 3/8)	
D-406-2009	С	Yellow	12 - 10 AWG	3.0 - 6.0 (12 - 10)	43.0 (1.70)	10.0 (0.39)	6.5 (0.255)	2.8 (0.110)	3.50 (0.138)	10 to 13 (3/8 to 1/2)	

MATERIALS

- 1. INSULATION SLEEVE: Heat-shrinkable, radiation cross-linked polyamide (nylon) with a polyamide-based hot-melt adhesive liner. Color per table.
- 2. CRIMP SPLICE: Tin-plated copper alloy.

BASE METAL: C110 Copper.

PLATING: Tin-plated per MIL-T-10727, Type 1.

APPLICATION

- 1. These parts may be used to obtain an environment-resistant one-to-one in-line (butt) splice in wires meeting the size range and diameter restraints specified herein and having a temperature rating of not less than 85°C.
- 2. ØA* (a) Minimum diameter as received: Wire insulation diameter must be less than this value.
 - (b) Maximum diameter after recovery: Wire insulation diameter must be larger than this value to obtain an environment resistant splice.
- 3. Wires are to be stripped per table, inserted into opposite ends of the crimp barrel, crimped with a Tyco Electronics/Raychem AD-1522 tool (or equivalent). The sleeve must be heated along its whole length until the crimp marks are gone and the ends of the sleeve recover onto the wires.
- 4. Spliced assemblies will meet the requirements of Raychem specification RB-107.
- 5. The parts covered by this drawing are UL (US and CANADA) Listed, File #E87681.

300 Con		300 Const	tronics Corporation titution Drive, rk, CA. 94025, U.S.A.		Raychem	DURASEAL CRIMP SPLICE, ENVIRONMENT RESISTANT					
Unless otherwise specified dimensions are in millimeters. [Inches dimensions are shown in brackets]						D-406-2007/-2008/-2009					
TOLERANCES:	ANGI	GLES: N/A Tyco Electronics reserves the right to amend									
0.00 N/A 0.0 N/A 0 N/A	ROUGHNESS IN MICRON		this drawing at any time. Users should evaluate the suitability of the product for their application.		PROD. REV.: SEE TABLE		DOC. ISSUE:	DATE: 09-Nov-05			
PREPARED BY:	PREPARED BY: DCR NUM		BER:	REPLACES:		CAGE CODE :		SCALE:	SIZE:	SHEET:	
lrodriguez		D050474			D030202	06090			A	1 of 1	