





TE Product Code /Product Marking	TE Part No.(RPN)	Conductor (AWG/MCM)	Dimensions in Inch (mm)							End Cap Color	Die Index No	No. of Crimp
			(øE) (Stud Hole)	Stud Hole Spacing	(øA) (Barrel ID)	(øC) (Barrel OD)	(B) (Barrel Length)	(D) (Palm Width)	(J) (Total Length)			
TATL2-1/0-3/8-U	EN3750-401	1/0	3/8	1.75 (44.5)	0.42 (10.67)	0.64 (16.26)	1.5 (38.1)	0.88 (22.36)	5.28 (134.12)	Tan	296	2
TATL2-1/0-1/2-U	EN3750-018	1/0	1/2	1.75 (44.5)	0.42 (10.67)	0.64 (16.26)	1.5 (38.1)	0.88 (22.36)	5.28 (134.12)	Tan	296	2
TATL2-2/0-3/8-U	EN4520-136	2/0	3/8	1.75 (44.5)	0.44 (11.2)	0.69 (17.53)	1.5 (38.1)	0.95 (24.2)	5.5 (139.7)	Olive	296	2
TATL2-2/0-1/2-U	EN3750-326	2/0	1/2	1.75 (44.5)	0.44 (11.2)	0.69 (17.53)	1.5 (38.1)	0.95 (24.2)	5.5 (139.7)	Olive	296	2
TATL2-3/0-3/8-U	EN4520-137	3/0	3/8	1.75 (44.5)	0.49 (12.45)	0.76 (19.31)	1.5 (38.1)	1.06 (26.93)	5.5 (139.7)	Ruby	467	2
TATL2-3/0-1/2-U	EN3750-327	3/0	1/2	1.75 (44.5)	0.49 (12.45)	0.76 (19.31)	1.5 (38.1)	1.06 (26.93)	5.5 (139.7)	Ruby	467	2
TATL2-4/0-1/2-U	EN3750-019	4/0	1/2	1.75 (44.5)	0.54 (13.72)	0.87 (22.1)	1.94 (49.28)	1.19 (30.23)	6.0 (152.4)	white	298	2
TATL2-4/0-5/8-U	EN4520-143	4/0	5/8	1.75 (44.5)	0.54 (13.72)	0.87 (22.1)	1.94 (49.28)	1.19 (30.23)	6.0 (152.4)	white	298	2
TATL2-250-1/2-U	EN3750-391	250	1/2	1.75 (44.5)	0.6 (15.24)	0.91 (23.12)	1.94 (49.28)	1.25 (31.75)	6.0 (152.4)	white	298	2
TATL2-250-5/8-U	EN4520-138	250	5/8	1.75 (44.5)	0.6 (15.24)	0.91 (23.12)	1.94 (49.28)	1.25 (31.75)	6.0 (152.4)	white	298	2
TATL2-300-1/2-U	EN3750-930	300	1/2	1.75 (44.5)	0.65 (16.51)	1.01 (25.66)	2.25 (57.15)	1.38 (35.06)	6.56 (166.63)	Blue	470	2
TATL2-350-1/2-U	EN3750-377	350	1/2	1.75 (44.5)	0.73 (18.55)	1.11 (28.2)	2.25 (57.15)	1.5 (38.1)	6.56 (166.63)	Brown	299	2
TATL2-350-5/8-U	EN4520-139	350	5/8	1.75 (44.5)	0.73 (18.55)	1.11 (28.2)	2.25 (57.15)	1.5 (38.1)	6.56 (166.63)	Brown	299	2
TATL2-400-1/2-U	EN3750-931	400	1/2	1.75 (44.5)	0.76 (19.4)	1.18 (30)	2.5 (63.5)	1.62 (41.2)	6.88 (174.8)	Green	472	6
TATL2-500-1/2-U	EN3750-378	500	1/2	1.75 (44.5)	0.85 (21.59)	1.32 (33.53)	3.0 (76.2)	1.75 (44.45)	7.31 (185.68)	Pink	300	6
TATL2-500-5/8-U	EN4520-140	500	5/8	1.75 (44.5)	0.85 (21.59)	1.32 (33.53)	3.0 (76.2)	1.75 (44.45)	7.31 (185.68)	Pink	300	6
TATL2-600-1/2-U	EN3750-064	600	1/2	1.75 (44.5)	0.93 (23.63)	1.44 (36.58)	3.0 (76.2)	1.75 (44.45)	7.31 (185.68)	Black	473	6
TATL2-750-1/2-U	EN3750-379	750	1/2	1.75 (44.5)	1.04 (26.42)	1.5 (38.1)	3.38 (85.86)	2 (50.8)	8.25 (209.55)	Gray	303	6
TATL2-1000-1/2-U	ER4520-201	1000	1/2	1.75 (44.5)	1.19 (30.3)	1.84 (46.8)	4.62 (117.4)	2.44 (62.0)	9.68 (245.8)	Brown	302	7
TATL2-1000-9/16-U	EN4520-209	1000	9/16	1.75 (44.5)	1.19 (30.3)	1.84 (46.8)	4.62 (117.4)	2.44 (62.0)	9.68 (245.8)	Brown	302	7
TATL2-1000-5/8-U	EN4520-208	1000	5/8	1.75 (44.5)	1.19 (30.3)	1.84 (46.8)	4.62 (117.4)	2.44 (62.0)	9.68 (245.8)	Brown	302	7
TATL2-1000-3/4-U	EN4520-210	1000	3/4	1.75 (44.5)	1.19 (30.3)	1.84 (46.8)	4.62 (117.4)	2.44 (62.0)	9.68 (245.8)	Brown	302	7
TATL2-1250-1/2	EN4520-202	1250	1/2	1.75 (44.5)	1.33 (33.7)	1.84 (46.8)	4.62 (117.3)	2.6 (66.0)	9.68 (245.8)	Brown	302	7
TATL2-1250-5/8	EN4520-211	1250	5/8	1.75 (44.5)	1.33 (33.7)	1.84 (46.8)	4.62 (117.3)	2.6 (66.0)	9.68 (245.8)	Brown	302	7
TATL2-1250-3/4	EN4520-212	1250	3/4	1.75 (44.5)	1.33 (33.7)	1.84 (46.8)	4.62 (117.3)	2.6 (66.0)	9.68 (245.8)	Brown	302	7
TATL2-1500-1/2	EN4520-203	1500	1/2	1.75 (44.5)	1.5 (38.0)	2.24 (57.0)	4.62 (117.3)	3.07 (78.0)	9.91 (251.7)	Blue	478	3
TATL2-1500-5/8	EN4520-213	1500	5/8	1.75 (44.5)	1.5 (38.0)	2.24 (57.0)	4.62 (117.3)	3.07 (78.0)	9.91 (251.7)	Blue	478	3
TATL2-1500-3/4	EN4520-204	1500	3/4	1.75 (44.5)	1.5 (38.0)	2.24 (57.0)	4.62 (117.3)	3.07 (78.0)	9.91 (251.7)	Blue	478	3

NOTE:

1. MATERIAL: ALUMINUM
2. FINISH: ELECTRO TIN PLATED
3. WITHOUT INSPECTION WINDOW
4. PRE-FILLED WITH ANTI OXIDANT COMPOUND
5. COLOR-CODED END CAPS INSERTED IN BARREL END
6. FOR COPPER OR ALUMINIUM CONDUCTOR
7. INSERT ONE INSTALLATION INSTRUCTION IN EACH STANDARD PACKAGE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
INCHES (mm)			
		0 PLC	$\pm -$
		1 PLC	$\pm -$
		2 PLC	$\pm -$
		3 PLC	$\pm -$
		4 PLC	$\pm -$
		ANGLES	$\pm -$
MATERIAL		FINISH	
SEE NOTES		SEE NOTES	

DWN	01DEC2020	 TE Connectivity			
RAVL.S					
CHK	01DEC2020				
J.OPEL					
APVD	01DEC2020	NAME			
J.OPEL		DUAL RATED ALUMINUM CRIMP LUGS 2 HOLE —			
PRODUCT SPEC					
—					
APPLICATION SPEC					
—					
WEIGHT	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		A3	00779	C-E00001661	—
CUSTOMER DRAWING				SCALE	REV
				NTS	C
				SHEET	1 OF 1