


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL REL PER RTS#1620495	06OCT2021	RS	BJ



DESCRIPTION	TE Part No. (RPN)	Conductor (AWG/MCM)	Dimensions in Inch (mm)			END CAP Color	Die Index No.	No. of Crimp per side
			øA (Barrel ID)	øC (Barrel OD)	J (Total Length)			
TASL-6-U	EN3750-381	6	0.20 (5.1)	0.35 (8.8)	1.62 (41.1)	Gray	346	2
TASL-4-U	EN3750-382	4	0.26 (6.7)	0.47 (11.9)	2.12 (53.8)	Green	375	2
TASL-2-U	EN3750-383	2	0.31 (7.8)	0.53 (13.5)	2.0 (50.8)	Pink	348	2
TASL-1-U	EN3750-076	1	0.35 (8.9)	0.53 (13.5)	2.0 (50.8)	Pink	348	2
TASL-1/0-U	EN3750-384	1/0	0.41 (10.5)	0.64 (16.3)	2.12 (53.8)	Tan	296	2
TASL-2/0-U	EN3750-385	2/0	0.44 (11.2)	0.69 (17.5)	2.31 (58.7)	Olive	296	2
TASL-3/0-U	EN3750-386	3/0	0.48 (12.3)	0.76 (19.3)	2.62 (66.5)	Ruby	467	2
TASL-4/0-U	EN3750-387	4/0	0.54 (13.7)	0.87 (22.2)	2.75 (69.9)	White	298	2
TASL-250-U	EN4520-024	250	0.59 (15.1)	0.91 (23.0)	2.94 (74.7)	White	298	2
TASL-300-U	EN4520-025	300	0.65 (16.5)	1.01 (25.7)	3.12 (79.2)	Blue	470	2
TASL-350-U	EN4520-026	350	0.72 (18.3)	1.11 (28.1)	3.38 (85.8)	Brown	299	2
TASL-500-U	EN3750-388	500	0.84 (21.4)	1.32 (33.5)	3.88 (98.6)	Pink	300	4
TASL-600-U	EN4520-027	600	0.92 (23.4)	1.44 (36.5)	4.12 (104.6)	Black	473	4
TASL-750-U	EN3750-389	750	1.03 (26.2)	1.5 (38.1)	4.68 (118.8)	Gray	936	4
TASL-1000-U	EN4520-205	1000	1.19 (30.3)	1.84 (46.76)	5.25 (133.4)	Brown	302	4
TASL-1250	EN4520-206	1250	1.33 (33.7)	1.84 (46.76)	6.21 (157.73)	Brown	302	4
TASL-1500	EN4520-207	1500	1.5 (38.0)	2.2 (57.0)	7.1 (180.0)	Blue	478	3

NOTE:
1. MATERIAL: EC GRADE ALUMINIUM
2. FINISH: ELECTRO TIN PLATED
3. FOR COPPER OR ALUMINIUM CONDUCTOR
4. PRE-FILLED WITH ANTI OXIDANT COMPOUND
5. COLOR-CODED END CAPS INSERTED IN BARREL END
6. INSERT ONE INSTALLATION INSTRUCTION IN EACH STANDARD PACKAGE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES(mm)

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL
SEE NOTES

FINISH
SEE NOTES

DWN RAVI.S 06OCT2021
CHK J.GUPPY 06OCT2021
APVD J.OPEL 06OCT2021

PRODUCT SPEC
—
APPLICATION SPEC
—
WEIGHT —

CUSTOMER DRAWING

TE Connectivity

NAME
DUAL RATED ALUMINUM SPLICES

SIZE
A3

CAGE CODE
00779

DRAWING NO
E00001683

RESTRICTED TO
—

SCALE
NTS

SHEET
1 OF 1

REV
A