

4

3


2

1


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION. ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	B	NEW DRAWING FORMAT	09DEC2016	GK KM

### PRESENTATION




### PRINTING/DIMENSION



RADIUS = 4 x .060 inch [4 x 1.5 mm]

### LABEL BUILD DETAIL



All dimensions in Inches [mm]

MATERIAL	THERMAL TRANSFER PRINTABLE PAPER
ADHESIVE TYPE	ACRYLIC PERMANENT
NOM THICKNESS	0.07 MM [.003 INCH]
BACKGROUND COLOURS	WHITE
WOUND	OUTSIDE WOUND

<b>TOLERANCES INCH[mm]</b> LABEL HEIGHT: ±.018 [0.3] LABEL WIDTH: ±.018 [0.3] WEB WIDTH: ±.039 [1.0] VERTICAL REPEAT: ±.039 [1.0] HORIZONTAL REPEAT: ±.039 [1.0] PRINT POSITIONING: ±.039 [1.0] *NON ACCUMULATING	THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: INCHES[mm]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	DWN 09DEC2016 GOPALAKRISHNA HV CHK 09DEC2016 K. MUNZ APVD 09DEC2016 K. MUNZ PRODUCT SPEC APPLICATION SPEC WEIGHT CUSTOMER DRAWING	TE Connectivity EP ECONOMY PAPER LABEL SIZE A2 CAGE CODE 00779 DRAWING NO C-EP-508318-2.5-9 RESTRICTED TO SCALE NTS SHEET 1 of 1 REV B
--	--	---	--	---

EP-508318-2.5-9