

Number of skirts per core						
kV	Indoor	Outdoor				
12	0	1				
17.5	0	1				
24	0	3				
36	0	4				
42	0	4				

Mini clearances	Max. Sy:	stem voltage ir	Max. System voltage in kV		
	12	17.5	24	36	42
a Air Clarence	as fo	r local specific	as for local specification		
b ph/ph and ph/ground in mm	15	20	25	35	45
d Between skirts in mm	10	15	20	25	45
r (min.bending radius)=15xD					

	THIS DRAWING IS A C	DWN 06MAR2020 RAGHAVENDRA K CHK 06MAR2020 JORDI V			TE Connectivity					
	DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD JORDI V	06MAR2020	IXSU OXSU SHRINKABLE TERMINATIONS			`		
-		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± -	PRODUCT SPEC — APPLICATION SPEC					VATIONS		
	~	4 PLC \pm – ANGLES \pm –	_		SIZE	CAGE CODE	DRAWING NO			RESTRICTED TO
	MATERIAL	FINISH	WEIGHT	_	A3	00779	C -EPD-202	2-0XSU/IXS	SU-01	_
		_	CUSTOMER D	RAWING			SCALE	NTS SHEET	1 OF 1	REV 1