
DCPT (3:1 RATIO) (Yellow/Green Striped)

Single Wall Dual Colour tube. A Premium grade heat shrink tube primarily used for electrical insulation. Has a UL224 approval and several Military related approvals.



PRODUCT DIMENSIONS

SIZE	Inside Diameter as supplied (min) mm (inch) D	Inside Diameter after recovery (max) mm (inch) d	Wall Thickness after recovery (nom) mm (inch) W	Wall Thickness Tolerance after recovery mm (inch)
3/1	3.0 (0.118)	1.0 (0.039)	0.55 <i>(0.021)</i>	0.10 (0.004)
6/2	6.0 <i>(0.236)</i>	2.0 (0.078)	0.65 <i>(0.026)</i>	0.10 (0.004)
9/3	9.0 <i>(0.354)</i>	3.0 (0.118)	0.75 <i>(0.029)</i>	0.15 (0.006)
12/4	12.0 <i>(0.472)</i>	4.0 (0.157)	0.75 <i>(0.029)</i>	0.15 (0.006)
18/6	18.0 <i>(0.708)</i>	6.0 <i>(0.236)</i>	0.85 <i>(0.033)</i>	0.15 <i>(0.006)</i>
24/8	24.0 <i>(0.944)</i>	8.0 (0.314)	1.00 (0.039)	0.20 (0.007)

DCPT (3:1 RATIO)				-				
(Yellow/Green striped) STANDARD SIZE REFERENCE DIMENSIONAL DRAWING				for the second of	TE Connectivity Ltd. family of All Rights Reserved	companies		
				DIMENSIONS IN	TITLE			
				mm (Inch)	DCPT (3:1	RATIO) (Yellow/Green str	riped) –	
				Ф		O MODIFIED POLYOLEFIN LL HEAT SHRINK TUBING		
				SHEET	NO		REV	
REV	ENGINEERING CHANGE	CHK	DATE	1 of 2	DCPT (3:1	RATIO) – Standard sizes	Α	

DCPT (3:1 RATIO) (Yellow/Green Striped)

PRODUCT INFORMATION

General use single wall Polyolefin Tubing.
Shrink Ratio – 3:1

Longitudinal Shrinkage on full recovery – 5 to -10%
Material conforms to TE Specification RW-2056
Standard Colour: Yellow/Green stripe
Flame Retardant

Tubing cut to specific lengths can be supplied from the product sizes referenced within this drawing.

Cut length tolerances are as per the following table:

STANDARD CUTTING TOLERANCES (mm)				
CUT LENGTH	TOLERANCE			
Up to 9.9mm	±0.5mm			
10mm to 24.9mm	±1.0mm			
25mm to 54.9mm	±1.5mm			
55mm to 99.9mm	±3.0mm			
100mm to 149.9mm	±4.0mm			
150mm to 499.9mm	±5.0mm			
500mm to 1200mm	±12.5mm			

