

1. TECHNICAL CHARACTERISTICS:
 RATED VOLTAGE: 1500V
 RATED CURRENT: 350A
 INSULATION RESISTANCE: $\geq 5000\text{M}\Omega$
 RATED WITHSATAND VOLTAGE: 6.8KV
 POLLUTION DEGREE: 3
 CONTACT RESISTANCE: $< 0.15\text{m}\Omega$
 PROTECTION CLASS: IP67 (MATED)
 MATING CYCLES: 500 CYCLES
 OPERATION TEMPERATURE: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$
 COLOR: ORANGE / BLACK
 CODING: A/B

1. 技术参数:

额定电压:	1500V
额定电流:	350A
绝缘电阻:	>=5000MΩ
额定耐受电压:	6.8KV
污染等级:	3
接触电阻:	<0.15mΩ
防护等级:	IP67(配合)
插拔次数:	500次
工作温度:	-40℃~+125℃
颜色:	橙色 / 黑色
键位:	A/B

Technical drawing of a square plate with a central hole and four corner holes. The overall dimensions are 24.5 units by 24.5 units. The central hole has a diameter of $\varnothing 22.5$. The four corner holes have a diameter of $4 \times \varnothing 4.2$. The drawing includes dimension lines and leader lines indicating the sizes and positions of the holes.



TE Connectivity

HPC-350-M-R-XX-01-X-X

SIZE	CAGE CODE	DRAWING NO	RESTRICTED
A2	00779	C-H10311XX50X000	-

CUSTOMER DRAWING	SCALE	1	SHEET	1	OF	1	REV	A
------------------	-------	---	-------	---	----	---	-----	---