
REVISION							
REV	DESCRIPTION	DATE	APPROVED				
C2	ADDED SIZE 4 TO TABLE, SEE ECO-20-002059	2/12/2020	I.MYONG				



As Supplied As Recovered										
Inside Diameter 'I			Inside Diameter 'd' Wall Thickness 'W'							
Size	Minimum		Maximum		Minimum		Maximum		Nominal	
	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.
1/8 /5	.125	3.18	.062	1.57	.023	0.58	.037	0.99	.030	0.76
3/16/5	.187	4.75	.094	2.39	.026	0.66	.040	1.02	.033	0.83
1/4 /5	.250	6.35	.125	3.18	.028	0.71	.042	1.07	.035	0.89
3/8	.375	9.52	.187	4.75	.032	0.81	.048	1.21	.040	1.02
1/2	.500	12.70	.250	6.35	.040	1.02	.056	1.42	.048	1.21
3/4	.750	19.05	.375	9.52	.046	1.16	.068	1.72	.057	1.45
1	1.000	25.40	.500	12.70	.059	1.49	.081	2.05	.070	1.78
1-1/2	1.500	38.10	.750	19.05	.079	2.00	.111	2.81	.095	2.41
2	2.000	50.80	1.000	25.40	.094	2.38	.126	3.20	.110	2.79
3	3.000	76.20	1.500	38.10	.105	2.66	.145	3.68	.125	3.18
4	4.000	101.60	2.000	50.80	.120	3.05	.160	4.05	.140	3.55

## Raychem Harness & Components CUSTOMER DRAWING

		3		& Components	000	STOWER DIVAVING
				₹ TE		TE Connectivity
	TE CONNECTIVITY CORPORATION RESERVES THE RIGHT TO AMEND THIS DRAWING AT ANYTIME. USER SHOULD EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.			DR-25 HEAT-SHRINKABLE TUBING		
				DR-25		
	DRAWN: 10Dec2019 G.ROSITANO	APPROVED: 12Dec2019 I.MYONG	CAGE CODE 06090	CAD FILE: DR-25_cd	SIZE: A	SCALE: THIRD ANGLE PROJ. SHEET:  1_OF_2

## **NOTES**

- 1. THIS PRODUCT IS DESIGNED FOR A WIDE RANGE OF APPLICATIONS AND MEETS THE REQUIREMENTS OF TE SPECIFICATIONS RT-1116, AND RK-6008/1.
- 2. PACKAGED AND SUPPLIED ON A SPOOL OR AS A STICK. LABELED WITH PART NUMBER: DR-25= PRODUCT FAMILY, -3/8= ORDER SIZE, -0= BLACK (STANDARD COLOR). PACKAGING= -SP (SPOOL) OR -STK (STICK), Example: DR-25-3/8-0-SP.
- 3. ALWAYS ORDER THE LARGEST SIZE THAT WILL FIT SNUGGLY OVER THE COMPONENT TO BE COVERED.
- 4. FOR MATERIAL AND FINISH INFORMATION, REFER TO TE SPECIFICATIONS RT-1116 and RK-6008/1. FOR SPECIAL ORDER SIZES, CONTACT TE CONNECTIVITY.



## **REQUIREMENTS:**

THESE SIZES AS SPECIFIED, SHALL MEET THE REQUIREMENTS OF TE SPECIFICATION RT-1116 EXCEPT AS FOLLOWS:

5a. FLAMMABILITY:

SHALL BE SELF-EXTINGUISHING WHEN TESTED AS FOLLOWS:

AN 18 INCH SPECIMEN OF TUBING SHALL BE RECOVERED OVER A 21 INCH METAL ROD WITH A DIAMETER EQUIVALENT TO THE MAXIMUM RECOVERED DIAMETER SPECIFIED ABOVE. THE SPECIMEN SHALL THEN BE SUBJECTED TO THE VERTICAL TEST IN ACCORDANCE WITH ASTM D 2671, PROCEDURE B. THE TUBING SHALL BE CONSIDERED SELF—EXTINGUISHING ONLY IF IT EXTINGUISHES WITHIN 1 MINUTE AFTER THE FINAL REMOVAL OF THE GAS FLAME, AND NOT MORE THAN 25% OF THE INDICATOR FLAG IS BURNED OR CHARRED. BROWN SCORCHING OR SOOT ON THE INDICATOR FLAG SHALL NOT BE CAUSE FOR REJECTION.

- 5b. LOW TEMPERATURE FLEXIBILITY:

  SHALL BE IN ACCORDANCE WITH RT-1116, PARAGRAPH 4.3.3,
  USING A 3/8 INCH MANDREL.
- 5c. SHORE HARDNESS: DOES NOT APPLY.

## **CUSTOMER DRAWING**Raychem Harness & Components

**STE** TE Connectivity TITLE: DR-25 HEAT-SHRINKABLE TUBING TE CONNECTIVITY DRAWING NO: REV: DRAWING AT ANYTIME. ER SHOULD EVALUATE
E SUITABILITY OF THE
PRODUCT FOR THEIR **DR-25** C2 DRAWN: GMR CAGE CODE SIZE: THIRD ANGLE PROJ. APPLICATION. 12/10/2019 06090  $\oplus \triangleleft$ 

© 2019-2020 TE Connectivity Corporation. All Rights reserved.