

REV: DATE: B Feb 6, 2018

REV PER ECO 17-018324





### **KIT DESCRIPTION**

ITEM	DESCRIPTION	MATERIAL
1	BODY ASSEMBLY - 90° SWEPT	ALUMINIUM ALLOY
2	CLAMPING NUT - PLAIN	ALUMINIUM ALLOY
3	CONIC RING	ALUMINIUM ALLOY
4	STAR	ALUMINIUM ALLOY

© 2006 Tyco Electronics Corporation. All rights reserved.


Wire and Harnessing Products			Raychem Wire and Harnessing Products 300 Constitution Drive Menlo Park, CA 94025 USA	HEXASHIELD SWEPT ADAPTOR FOR CODE 40 CONNECTORS- PLAIN CLAMPING NUT				
DIMENSIONS ARE IN property of Tyco Electric confidence. Publication			nformation set forth hereon is the onics and is to be held in trust and n, duplication, disclosure or use for expressly authorized in writing by hibited.	HEX40-A	Y-90S-	YY-AY	Y-1-YY	
DRAWN: IRT	DATE: SEP 00		ves the right to amend this drawing at devaluate the suitability of the atton.	FILE-UK: HEX40-90S-US	File & DCR D060244	SCALE: NONE	SHEET: 1 OF 4	

REV:	DATE:
В	Feb 6, 2018

#### **TABLE OF DIMENSIONS**

Order Number	Shell Size		ØA Thread Class 6H	<b>ØB</b> Max	<b>ØC</b> Max	<b>D</b> Max	E Max	_	rule ntity
	Mil.	Com.						Std.	Opt.
09	Α	09	M12 x 1	19.0 [0.75"]	17.5 [.689]	15.0 [0.59"]	32.0 [1.26"]	1	-
11	В	11	M15 x 1	22.0 [0.87"]	21.5 [.846]	16.0 [0.63"]	33.0 [1.30"]	2	-
13	С	13	M18 x 1	25.5 [1.00"]	22.5 [.886]	19.0 [0.75"]	34.0 [1.34"]	3	-
15	D	15	M22 x 1	30.5 [1.20"]	28.5 [1.122]	19.0 [0.75"]	34.0 [1.34"]	5	-
17	Е	17	M25 x 1	33.5 [1.32"]	31.5 [1.240]	21.0 [0.83"]	35.0 [1.38"]	6	7
19	F	19	M28 x 1	37.0 [1.46"]	35.0 [1.378]	23.0 [0.91"]	37.0 [1.46"]	7	-
21	G	21	M31 x 1	38.5 [1.52"]	38.0 [1.496]	23.0 [0.91"]	39.0 [1.54"]	9	11
23	Н	23	M34 x 1	42.0 [1.65"]	41.0 [1.614]	28.0 [1.10"]	42.0 [1.65"]	10	13
25	J	25	M37 x 1	46.5 [1.83"]	46.0 [1.811]	28.0 [1.10"]	42.0 [1.65"]	12	17

#### **PART NUMBERING**



### **APPLICATION**


- These adaptors are designed to be mounted on the following connectors:

MIL-C-38999 Series III and IV

<b>tyco</b>   Electronics Wire and Harnessing Products			Raychem Wire and Harnessing Products 300 Constitution Drive Menlo Park, CA 94025 USA	HEXASHIELD SWEPT ADAPTOR FOR CODE 40 CONNECTORS- PLAIN CLAMPING NUT				
DIMENSIONS ARE IN  MILLIMETERS  property of Tyco Electric confidence. Publication		nformation set forth hereon is the onics and is to be held in trust and n, duplication, disclosure or use for expressly authorized in writing by hibited.	HEX40-A	Y-90S-	YY-AY	Y-1-YY		
DRAWN: IRT	DATE: SEP 00		ves the right to amend this drawing at devaluate the suitability of the ation.	FILE-UK: HEX40-90S-US	File & DCR D060244	SCALE: NONE	SHEET: 2 OF 4	

REV: DATE: B Feb 6. 2018

- They are qualified to the Raychem specification RB-114, when installed on metallic Mil-Specification circular connectors only.
- They are designed primarily for open wire bundle installation but are also designed to accept Raychem heat shrink moulded parts where strain relief is required see illustration on sheet 3.



- Use in conjunction with the ferrules HET-A-0XX, which are purchased separately. Refer to HET-A-0XX S.C.D. for relevant selection details.

### **INSTALLATION**

- See Installation Procedure RPIP-696-04.

### **PACKAGING**


- All components are supplied in a plastic bag.

<b>Type</b> Electronics Wire and Harnessing Products			Raychem Wire and Harnessing Products 300 Constitution Drive Menlo Park, CA 94025 USA	HEXASHIELD SWEPT ADAPTOR FOR CODE 40 CONNECTORS- PLAIN CLAMPING NUT				
DIMENSIONS ARE IN property of Tyco Electric confidence. Publication		nformation set forth hereon is the onics and is to be held in trust and n, duplication, disclosure or use for expressly authorized in writing by hibited.	DOCUMENT NO.  HEX40-A	Y-90S-	YY-AY	Y-1-YY		
DRAWN: IRT	DATE: SEP 00		ves the right to amend this drawing at devaluate the suitability of the atton.	FILE-UK: HEX40-90S-US	File & DCR D060244	SCALE: NONE	SHEET: 3 OF 4	

REV:	DATE:
В	Feb 6. 2018

#### NOTES!

- 1. Item 4 Star is **not** supplied with Hexashield Order Number 09.
- 2. The DS option, illustrated below, is for a Drilled Star that is available on sizes 15 to 25 only. This option is to allow unshielded wires to pass through the assembly.




STAR SIZE	15	17	19	21	23	25
ØD MAX	3.0	6.0	9.0	12.0	15.0	18.0
	[0.12"]	[0.24"]	[0.35"]	[0.47"]	[0.59"]	[0.71"]

3. Where the ferrule quantities required are standard, the item 4 - Star - is also standard. If the optional quantity is selected then 2 items 4 will be supplied - one "split" and the other one standard. See sheet 4 for illustration.

**EXAMPLE: FERRULE QUANTITY CODE -A13** 

-A13 = -A10 SPLIT STAR + -A3 STANDARD STAR



4. Assembly is to be permanently marked with Code Identity Number and Part Number. (e.g. 06090 HEX40-AB-90S-21-A9-1)

tц	CO	/	Ele	ctr	or	ics

Wire and Harnessing Products

DIMENSIONS ARE IN **MILLIMETERS** 

INCH DIMENSIONS ARE SHOWN IN **BRACKETS** 

DRAWN: DATE: **IRT** SEP 00

Raychem Wire and Harnessing Products 300 Constitution Drive Menlo Park, CA 94025 USA

**HEXASHIELD SWEPT ADAPTOR** FOR CODE 40 CONNECTORS-**PLAIN CLAMPING NUT** 

UNLESS OTHERWISE SPECIFIED

confidence. Publication, duplication, disclosure or use for any other purpose not expressly authorized in writing by Tyco Electronics is prohibited.

> Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.

This drawing and the information set forth hereon is the property of Tyco Electronics and is to be held in trust and

DOCUMENT NO.

HEX40-AY-90S-YY-AYY-1-YY

FILE-UK: File & DCR SCALE: SHEET: D060244 HEX40-90S-US NONE 4 OF 4