


REV: REVISED PER DATE: B ECO-12-013539 July 26, 2012




STRAIGHT ADAPTOR
- 00









© 2012 Tyco Electronics Corporation, a TE Connectivity Ltd. Company. All Rights reserved.



TE Connectivity 300 Constitution Drive Menlo Park, CA 94025, USA

DOCUMENT NO.

HEX40-AY-YY-YY-AYY-2-YY

HEXASHIELD ADAPTOR FOR

CODE 40 CONNECTORS

(TINEL CLAMPING NUT)

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCH DIMENSIONS ARE SHOWN IN BRACKETS

DRAWN: DATE:
IRT FEB 03

Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.

 FILE:
 SCALE:
 SHEET:

 T31747
 NONE
 1 OF 4

	REVISED PER				
В	ECO-12-013539	July 26, 2012			

KIT DESCRIPTION

ITEM	DESCRIPTION	MATERIAL
1	BODY ASSEMBLY	ALUMINIUM ALLOY
2	TINEL CLAMPING ADAPTOR ASSEMBLY	ALUMINIUM ALLOY
	TINEL-LOCK™ RING	TINEL-X™
3	CONIC RING	ALUMINIUM ALLOY
4	STAR	ALUMINIUM ALLOY

TABLE OF DIMENSIONS

Order Number	Shell	Size	Tinel Entry	ØA Thread Class 6H	ØB Max	ØC Max	D Max	E Max	F Max	G Max		rule ntity
	Mil.	Com.	Size								Std.	Opt.
09	Α	09	05	M12 x 1	19.0 [0.75"]	38.5 [1.52"]	14.4 [.57"]	38.5 [1.52"]	17.9 [.70"]	42.0 [1.65"]	1	,
11	В	11	08	M15 x 1	22.0 [0.87"]	38.5 [1.52"]	14.9 [.59"]	39.0 [1.54"]	19.4 [.76"]	43.5 [1.71"]	2	
13	С	13	10	M18 x 1	25.5 [1.00"]	38.5 [1.52"]	15.9 [.63"]	39.5 [1.56"]	20.9 [.82"]	45.0 [1.77"]	3	-
15	D	15	12	M22 x 1	30.5 [1.20"]	38.5 [1.52"]	16.4 [.65"]	40.5 [1.60"]	22.4 [.88"]	46.5 [1.83"]	5	-
17	Е	17	14	M25 x 1	33.5 [1.32"]	38.5 [1.52"]	16.9 [.67"]	41.0 [1.61"]	23.9 [.94"]	48.0 [1.89"]	6	7
19	F	19	16	M28 x 1	37.0 [1.46"]	38.5 [1.52"]	17.4 [.69"]	41.5 [1.63"]	25.4 [1.00"]	49.5 [1.95"]	7	8
21	G	21	18	M31 x 1	38.5 [1.52"]	38.5 [1.52"]	18.4 [.72"]	42.5 [1.67"]	27.4 [1.08"]	51.5 [2.03"]	9	11
23	Н	23	20	M34 x 1	42.0 [1.65"]	38.5 [1.52"]	18.9 [.745"]	43.0 [1.69"]	28.9 [1.14"]	53.0 [2.09"]	10	13
25	J	25	20	M37 x 1	46.5 [1.83"]	46.0 [1.81"]	19.9 [.785"]	51.5 [2.03"]	30.4 [1.20"]	62.0 [2.44"]	12	18

Tinel Entry Size	øs
05	10.97/11.13
	[0.432/0.438"]
80	15.72/15.91
	[0.619"/0.626"]
10	18.84/19.11
	[0.742"/0.752"]
12	22.02/22.28
	[0.867"/0.877"]


Tinel Entry Size	ØS
14	25.17/25.46 [0.991"/1.002"]
16	28.34/28.63 [1.116"/1.127"]
18	31.52/31.81 [1.241"/1.252"]
20	34.69/34.98 [1.366"/1.377"]

© 2012 Tyco Electronics Corporation, a TE Connectivity Ltd. Company. All Rights reserved.

TITLE: TE Connectivity **HEXASHIELD ADAPTOR FOR** 300 Constitution Drive **CODE 40 CONNECTORS** Menlo Park, CA 94025, USA (TINEL CLAMPING NUT) UNLESS OTHERWISE SPECIFIED DOCUMENT NO. DIMENSIONS ARE IN Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application. HEX40-AY-YY-YY-AYY-2-YY MILLIMETERS. INCH DIMENSIONS ARE SHOWN IN **BRACKETS** DRAWN: DATE: FILE: SCALE: SHEET: **IRT** FEB 03 T31747 NONE

REV: REVISED PER DATE: B ECO-12-013539 July 26, 2012

PART NUMBERING




APPLICATION

- These adaptors are designed to be mounted on the following connectors:

MIL-C-38999 Series III and IV

- They are qualified to the Raychem specification RB-114, when installed on metallic Mil-Specification circular connectors only.
- They are designed for wire bundle installations having an overall braid terminated by means of a Tinel-Lock™ ring*.
- They are also designed to accept Raychem heat shrink moulded parts where strain relief and sealing is required see illustrations.



- Use in conjunction with the ferrules HET-A-***, which are purchased separately. Refer to HET-A-*** S.C.D. for relevant selection details.
- * Refer to TR S.C.D. for further information on Tinel-Lock™ rings.

INSTALLATION

- See Installation Procedure RPIP-696-04.

© 2012 Tyco Electronics Corporation, a TE Connectivity Ltd. Company. All Rights reserved. TE Connectivity **HEXASHIELD ADAPTOR FOR** 300 Constitution Drive **CODE 40 CONNECTORS** Menlo Park, CA 94025, USA (TINEL CLAMPING NUT) UNLESS OTHERWISE SPECIFIED DOCUMENT NO. DIMENSIONS ARE IN Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the HEX40-AY-YY-YY-AYY-2-YY MILLIMETERS. product for their application. INCH DIMENSIONS ARE SHOWN IN **BRACKETS** DRAWN: DATE: FILE: SCALE: SHEET: FEB 03 T31747 NONE **IRT**


REV:	REVISED PER	DATE:
В	ECO-12-013539	July 26, 2012

PACKAGING

- All components are supplied in a plastic bag.

NOTES!

- 1. Item 4 Star is **not** supplied with Hexashield Order Number 09.
- 2. The DS option, illustrated below, is for a Drilled Star that is available on sizes 15 to 25 only. This option is to allow unshielded wires to pass through the assembly.




STAR SIZE	15	17 19		21	23	25	
ØJ MAX	3.0	6.0	9.0	12.0	15.0	18.0	
	[0.12"]	[0.24"]	[0.35"]	[0.47"]	[0.59"]	[0.71"]	

3. Where the ferrule quantities required are standard, the item 4 - Star - is also standard. If the optional quantity is selected then 2 items 4 will be supplied - one "split" and the other one standard*, See below for illustration.

EXAMPLE: FERRULE QUANTITY CODE -A13

-A13 = -A10 SPLIT STAR + -A3 STANDARD STAR



- * On Order Number 19 only, the Optional Ferrule quantity of 8 uses a "standard" star also.
- Assembly is to be permanently marked with Code Identity Number and Part Number. (e.g. 06090 HEX40-AB-00-21-A9-2)

© 2012 Tyco Electronics Corporation, a TE Connectivity Ltd. Company. All Rights reserved.



TE Connectivity 300 Constitution Drive Menlo Park, CA 94025, USA HEXASHIELD ADAPTOR FOR CODE 40 CONNECTORS (TINEL CLAMPING NUT)

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCH DIMENSIONS ARE SHOWN IN BRACKETS

DATE:

FEB 03

DRAWN:

IRT

Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.

DOCUMENT NO.

HEX40-AY-YY-YY-AYY-2-YY

| FILE: | SCALE: | SHEET: | NONE | 4 OF 4