

REV: Α

AUG 17, 2006



# STRAIGHT ADAPTOR <u>-00</u>



© 2006 Tyco Electronics Corporation. All rights reserved.

**HEXASHIELD ADAPTOR FOR** 

**CODE 40 CONNECTORS-**

**EXTENDED BODY AND PLAIN** 

**CLAMPING NUT** 

# **tyco** | Electronics

#### **Wire and Harnessing Products**

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCH DIMENSIONS ARE SHOWN IN **BRACKETS** 

DRAWN: **IRT**  DATE: JUN 00

Raychem Wire and Harnessing Products 300 Constitution Drive Menlo Park, CA 94025 USA

property of Tyco Electronics and is to be held in trust and

confidence. Publication, duplication, disclosure or use for any other purpose not expressly authorized in writing by

Tyco Electronics reserves the right to amend this drawing at

any time. Users should evaluate the suitability of the

Tyco Electronics is prohibited.

product for their application.

DOCUMENT NO. This drawing and the information set forth hereon is the

TITLE:

HEX40L-AY-00-YY-AYY-1-YY

FILE-UK: File & DCR# SCALE: SHEET: D060247 Hex40I-1scd-us.doc NONE 1 **OF 4** 

If this document is printed it becomes uncontrolled. Check for the latest revision.

| SPECIFICATION CONTROL DRAWING | REV: | DATE:<br>AUG 17, 2006 |
|-------------------------------|------|-----------------------|

### **KIT DESCRIPTION**

| ITEM | DESCRIPTION          | MATERIAL        |
|------|----------------------|-----------------|
| 1    | BODY ASSEMBLY        | ALUMINIUM ALLOY |
| 2    | CLAMPING NUT - PLAIN | ALUMINIUM ALLOY |
| 3    | CONIC RING           | ALUMINIUM ALLOY |
| 4    | STAR                 | ALUMINIUM ALLOY |

### **TABLE OF DIMENSIONS**

| Order<br>Number | Shell Size |      | <b>ØA Thread</b><br>Class 6H | <b>ØB</b><br>Max | <b>ØC</b><br>Max | _    | rule<br>ntity |
|-----------------|------------|------|------------------------------|------------------|------------------|------|---------------|
|                 | Mil.       | Com. |                              |                  |                  | Std. | Opt.          |
| 09              | Α          | 09   | M12 x 1                      | 19.0<br>[0.75"]  | 17.5<br>[0.69"]  | 1    | -             |
| 11              | В          | 11   | M15 x 1                      | 22.0<br>[0.87"]  | 21.5<br>[0.85"]  | 2    | -             |
| 13              | С          | 13   | M18 x 1                      | 25.5<br>[1.00"]  | 22.5<br>[0.89"]  | 3    | -             |
| 15              | D          | 15   | M22 x 1                      | 30.5<br>[1.20"]  | 25.5<br>[1.00"]  | 5    | -             |
| 17              | Е          | 17   | M25 x 1                      | 33.5<br>[1.32"]  | 28.5<br>[1.12"]  | 6    | 7             |
| 19              | F          | 19   | M28 x 1                      | 37.0<br>[1.46"]  | 31.5<br>[1.24"]  | 7    | -             |
| 21              | G          | 21   | M31 x 1                      | 38.5<br>[1.52"]  | 35.0<br>[1.38"]  | 9    | 11            |
| 23              | Н          | 23   | M34 x 1                      | 42.0<br>[1.65"]  | 38.0<br>[1.50"]  | 10   | 13            |
| 25              | J          | 25   | M37 x 1                      | 46.5<br>[1.83"]  | 41.0<br>[1.61"]  | 12   | 17            |

### **PART NUMBERING**

- CONNECTOR CODE NUMBER

HEX40 = MIL-C-38999 SERIES III AND IV

L = EXTENDED BODY

- MATERIAL CODE:

A = ALUMINIUM ALLOY

- PLATING CODE:

B = CADMIUM OLIVE DRAB TO QQ-P416

C = ELECTROLESS NICKEL TO MIL-C-26074

- BODY STYLE

00 = STRAIGHT

- ORDER NUMBER

- FERRULE QUANTITY CODE

- 1 = PLAIN CLAMPING NUT

- DS = DRILLED STAR - OPTIONAL - SEE NOTE 2

| <b>type</b> Electronics  Wire and Harnessing Products                                   |                 |  | Raychem Wire and<br>Harnessing Products<br>300 Constitution Drive<br>Menlo Park, CA 94025<br>USA  | CODE 4<br>EXTENDED             | IIELD ADAPTOR FOR<br>40 CONNECTORS-<br>ED BODY AND PLAIN<br>LAMPING NUT |                |                         |  |
|---|-----------------|--|---|--------------------------------|---|----------------|-------------------------|--|
| DIMENSIONS ARE IN  MILLIMETERS  property of Tyco Electronic confidence. Publication, du |                 |  | ormation set forth hereon is the<br>nics and is to be held in trust and<br>duplication, disclosure or use for<br>pressly authorized in writing by<br>bited. | DOCUMENT NO.  HEX40L-A         | Y-00-YY   | -AYY-1         | -YY                     |  |
| DRAWN:<br>IRT   | DATE:<br>JUN 00 |  | s the right to amend this drawing at evaluate the suitability of the on.  | FILE-UK:<br>Hex40l-1scd-us.doc | File & DCR#<br>D060247  | SCALE:<br>NONE | SHEET:<br>2 <b>OF 4</b> |  |


|                               | <br>      |                       |
|-------------------------------|-----------|-----------------------|
| SPECIFICATION CONTROL DRAWING | REV:<br>A | DATE:<br>AUG 17, 2006 |
|                               |           |                       |

### **APPLICATION**

- These adaptors are designed to be mounted on the following connectors:

MIL-C-38999 Series III and IV

- They are qualified to the Raychem specification RB-114, when installed on metallic Mil-Specification circular connectors only.
- They are designed primarily for open wire bundle installation but are also designed to accept Raychem heat shrink moulded parts where strain relief and sealing is required see illustration.



- Use in conjunction with the ferrules HET-A-0XX, which are purchased separately. Refer to HET-A-0XX S.C.D. for relevant selection details.

### **INSTALLATION**


- See Installation Procedure RPIP-696-04.

# **PACKAGING**

- All components are supplied in a plastic bag.

#### **NOTES!**

- 1. Item 4 Star is **not** supplied with Hexashield Order Number 09.
- 2. The DS option, illustrated below, is for a Drilled Star that is available on sizes 15 to 25 only. This option is to allow unshielded wires to pass through the assembly.



| STAR SIZE | 15      | 17      | 19      | 21      | 23      | 25      |
|-----------|---------|---------|---------|---------|---------|---------|
| ØD MAX    | 3.0     | 6.0     | 9.0     | 12.0    | 15.0    | 18.0    |
|           | [0.12"] | [0.24"] | [0.35"] | [0.47"] | [0.59"] | [0.71"] |

| <b>tuco</b>   Electronics Wire and Harnessing Products   |                 |   | Raychem Wire and<br>Harnessing Products<br>300 Constitution Drive<br>Menlo Park, CA 94025<br>USA | CODE 4<br>EXTENDED             | CASHIELD ADAPTOR FOR<br>CODE 40 CONNECTORS-<br>ENDED BODY AND PLAIN<br>CLAMPING NUT |                |                         |  |
|--|-----------------|---|--|--------------------------------|---|----------------|-------------------------|--|
| UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCH DIMENSIONS ARE SHOWN IN BRACKETS  This drawing and the information set forth hereon property of Tyco Electronics and is to be held in tree confidence. Publication, duplication, disclosure or any other purpose not expressly authorized in writty Tyco Electronics is prohibited. |                 | nics and is to be held in trust and<br>duplication, disclosure or use for<br>expressly authorized in writing by | DOCUMENT NO.  HEX40L-A   | Y-00-YY                        | -AYY-1  | -YY            |                         |  |
| DRAWN:<br>IRT  | DATE:<br>JUN 00 |   | s the right to amend this drawing at evaluate the suitability of the on.                         | FILE-UK:<br>Hex40I-1scd-us.doc | File & DCR#<br>D060247  | SCALE:<br>NONE | SHEET:<br>3 <b>OF 4</b> |  |

# SPECIFICATION CONTROL DRAWING


REV: Α

DATE: AUG 17, 2006

3. Where the ferrule quantities required are standard, the item 4 - Star - is also standard. If the optional quantity is selected then 2 items 4 will be supplied - one "split" and the other one standard. See below for illustration.

**EXAMPLE: FERRULE QUANTITY CODE -A13** 

-A13 = -A10 SPLIT STAR + -A3 STANDARD STAR



4. Assembly is to be permanently marked with Code Identity Number and Part Number. (e.g. 06090 HEX40L-AB-00-21-A9-1)



#### Wire and Harnessing Products

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCH DIMENSIONS ARE SHOWN IN **BRACKETS** 

DRAWN: DATE:

IRT JUN 00

Raychem Wire and Harnessing Products 300 Constitution Drive Menlo Park, CA 94025 USA

This drawing and the information set forth hereon is the property of Tyco Electronics and is to be held in trust and

confidence. Publication, duplication, disclosure or use for

Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the

any other purpose not expressly authorized in writing by

Tyco Electronics is prohibited.

product for their application.

TITLE:

**HEXASHIELD ADAPTOR FOR CODE 40 CONNECTORS-EXTENDED BODY AND PLAIN CLAMPING NUT** 

DOCUMENT NO.

HEX40L-AY-00-YY-AYY-1-YY

| FILE-UK:           | File & DCR# | SHEET: |
|--------------------|-------------|--------|
| Hex40l-1scd-us.doc | D060247     | 4 OF 4 |
|                    |             |        |

If this document is printed it becomes uncontrolled. Check for the latest revision.