

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECN-22-143143	17JUN2022	BN	JO
	A2	ECR-22-146951	20JUL2022	SM	JO

NOTE:
1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2 SUFFIX “-I” COMES WITH FACTORY APPLIED INHIBITOR.




Fig. 1




Fig. 2

Catalog No.	Part No.	Connection Type		Main			Tap			Dimensions in mm (in)		Tap Nut	Eye bolt material	Fig.
		Main	Tap	Diameter in mm (in)	AAC/CU	ACSR	Diameter in mm (in)	AAC/CU	ACSR	A	C			
THLA-2/0-2/0-P	EN3750-280	AL	AL/CU	3.25-10.51 (0.128-0.414)	#8 - 2/0	#8 - 1/0	3.25-10.51 (0.128-0.414)	#8 - 2/0	#8 - 1/0	114.3 (4.50)	72.4 (2.85)	3/8	SS	1
THLA-2/0-2/0-BP	EN4520-216	AL	AL/CU	3.25-10.51 (0.128-0.414)	#8 - 2/0	#8 - 1/0	3.25-10.51 (0.128-0.414)	#8 - 2/0	#8 - 1/0	114.3 (4.50)	72.4 (2.85)	3/8	Bronze	1
THLA-400-4/0-P	EN3750-281	AL	AL/CU	4.11-18.92 (0.162-0.745)	#6 - 400	#6 - 397.5	3.86-17.32 (0.152-0.682)	#6 - 4/0	#6 - 3/0	170.2 (6.70)	62.0 (2.44)	7/16	SS	2
THLA-400-4/0-BP	EN4520-217	AL	AL/CU	4.11-18.92 (0.162-0.745)	#6 - 400	#6 - 397.5	3.86-17.32 (0.152-0.682)	#6 - 4/0	#6 - 3/0	170.2 (6.70)	62.0 (2.44)	7/16	Bronze	2
2 THLA-2/0-2/0-P-I	EN4520-350	AL	AL/CU	3.25-10.51 (0.128-0.414)	#8 - 2/0	#8 - 1/0	3.25-10.51 (0.128-0.414)	#8 - 2/0	#8 - 1/0	114.3 (4.50)	72.4 (2.85)	3/8	SS	1
2 THLA-2/0-2/0-BP-I	EN4520-349	AL	AL/CU	3.25-10.51 (0.128-0.414)	#8 - 2/0	#8 - 1/0	3.25-10.51 (0.128-0.414)	#8 - 2/0	#8 - 1/0	114.3 (4.50)	72.4 (2.85)	3/8	Bronze	1
2 THLA-400-4/0-P-I	EN4520-347	AL	AL/CU	4.11-18.92 (0.162-0.745)	#6 - 400	#6 - 397.5	3.86-17.32 (0.152-0.682)	#6 - 4/0	#6 - 3/0	170.2 (6.70)	62.0 (2.44)	7/16	SS	2
2 THLA-400-4/0-BP-I	EN4520-348	AL	AL/CU	4.11-18.92 (0.162-0.745)	#6 - 400	#6 - 397.5	3.86-17.32 (0.152-0.682)	#6 - 4/0	#6 - 3/0	170.2 (6.70)	62.0 (2.44)	7/16	Bronze	2

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	09FEB2021	TE Connectivity			
				CHK	09FEB2021				
				APVD	09FEB2021	NAME			
				PRODUCT SPEC					
				APPLICATION SPEC		HOTLINE CLAMP ALUMINUM ALLOY 2/0-2/0 & 400-4/0			
				WEIGHT	-				
				CUSTOMER DRAWING		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
						A2	00779	C=E00001672	-
						SCALE	NTS	SHEET	1 OF 1
								REV	A2