


REV: DATE: B AUG 17 2006




STRAIGHT ADAPTOR

<u>-00</u>





45° ADAPTOR -45



© 2006 Tyco Electronics Corporation. All rights reserved.

-90

TITLE: **tyco** | Electronics Raychem Wire and **HEXASHIELD ADAPTOR FOR** Harnessing Products **CODE 41 CONNECTORS-**300 Constitution Drive **PLAIN CLAMPING NUT** Menlo Park, CA 94025 Wire and Harnessing Products USA This drawing and the information set forth hereon is the property of Tyco Electronics and is to be held in trust and confidence. Publication, duplication, disclosure or use for UNLESS OTHERWISE SPECIFIED DOCUMENT NO. DIMENSIONS ARE IN MILLIMETERS. HEX41-AY-YY-YY-AYY-1-YY any other purpose not expressly authorized in writing by INCH DIMENSIONS ARE SHOWN IN Tyco Electronics is prohibited. BRACKETS Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the DRAWN: DATE: FILE-UK: File & DCR# SCALE: SHEET: D060249 **CRJ** MAR 00 Hex41-1scd-us NONE 1 OF 4 product for their application.

REV:	DATE:
В	AUG 17 2006

KIT DESCRIPTION

ITEM	DESCRIPTION	MATERIAL
1	BODY ASSEMBLY	ALUMINIUM ALLOY
2	CLAMPING NUT – PLAIN	ALUMINIUM ALLOY
3	CONIC RING	ALUMINIUM ALLOY
4	STAR	ALUMINIUM ALLOY


TABLE OF DIMENSIONS

Order	Shell	Size	ØA Thread	ØB	ØС	D	E	F	G	_	rule
Number	Ser	Ser	UNEF 2B	Max	Max	Max	Max	Max	Max	Qua	ntity
	I	Ш								Std.	Opt.
09	09	80	0.4375"-28	19.0 [0.75"]	17.5 [0.69"]	12.5 [0.49"]	25.5 [1.00"]	16.0 [0.63"]	29.0 [1.14"]	1	-
11	11	10	0.5625"-24	22.0 [0.87"]	21.5 [0.85"]	13.0 [0.51"]	26.0 [1.02"]	17.5 [0.69"]	30.5 [1.20"]	2	-
13	13	12	0.6875"-24	25.5 [1.00"]	22.5 [0.89"]	14.0 [0.55"]	26.5 [1.04"]	19.0 [0.75"]	32.0 [1.26"]	3	-
15	15	14	0.8125"-20	30.5 [1.20"]	25.5 [1.00"]	14.5 [0.57"]	27.5 [1.08"]	20.5 [0.81"]	33.5 [1.32"]	5	-
17	17	16	0.9375"-20	33.5 [1.32"]	28.5 [1.12"]	15.0 [0.59"]	28.0 [1.10"]	22.0 [0.87"]	35.0 [1.38"]	6	7
19	19	18	1.0625"-18	37.0 [1.46"]	31.5 [1.24"]	15.5 [0.61"]	28.5 [1.12"]	23.5 [0.93"]	36.5 [1.44"]	7	-
21	21	20	1.1875"-18	38.5 [1.52"]	35.0 [1.38"]	16.5 [0.65"]	29.0 [1.14"]	25.5 [1.00"]	38.5 [1.52"]	9	11
23	23	22	1.3125"-18	42.0 [1.65"]	38.0 [1.50"]	17.0 [0.67"]	30.0 [1.18"]	27.0 [1.06"]	40.0 [1.57"]	10	13
25	25	24	1.4375"-18	46.5 [1.83"]	41.0 [1.61"]	18.0 [0.71"]	31.0 [1.22"]	28.5 [1.12"]	41.5 [1.63"]	12	17

tyce Electronics Wire and Harnessing Products			Raychem Wire and Harnessing Products 300 Constitution Drive Menlo Park, CA 94025 USA	HEXASHIELD ADAPTOR FOR CODE 41 CONNECTORS- PLAIN CLAMPING NUT			
DIMENSIONS ARE IN property of Tyco Electronic confidence. Publication, d			rmation set forth hereon is the ics and is to be held in trust and duplication, disclosure or use for pressly authorized in writing by pited.	DOCUMENT NO. HEX41-A	AY-YY-Y	Y-AYY- 1	I-YY
DRAWN: CRJ	DATE: MAR 00	Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.		FILE-UK: Hex41-1scd-us	File & DCR# D060249	SCALE: NONE	SHEET: 2 OF 4

REV: DATE: B AUG 17 2006

PART NUMBERING




APPLICATION

- These adaptors are designed to be mounted on the following connectors:

MIL-C-38999 Series I and II

- They are qualified to the Raychem specification RB-114, when installed on metallic Mil-Specification circular connectors only.
- They are designed primarily for open wire bundle installation but are also designed to accept Raychem heat shrink moulded parts where strain relief is required see illustration.



- Use in conjunction with the ferrules HET-A-0XX, which are purchased separately. Refer to HET-A-0XX S.C.D. for relevant selection details.

INSTALLATION

- See Installation Procedure RPIP-696-04.

PACKAGING


- All components are supplied in a plastic bag.

tyce Electronics Wire and Harnessing Products			Raychem Wire and Harnessing Products 300 Constitution Drive Menlo Park, CA 94025 USA	HEXASHIELD ADAPTOR FOR CODE 41 CONNECTORS- PLAIN CLAMPING NUT			
DIMENSIONS ARE IN property of Tyco Electronic confidence. Publication, of			rmation set forth hereon is the ilos and is to be held in trust and duplication, disclosure or use for pressly authorized in writing by bited.	HEX41-A	4Y-YY-Y	Y-AYY-1	I-YY
DRAWN: CRJ	DATE: MAR 00	Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.		FILE-UK: Hex41-1scd-us	File & DCR# D060249	SCALE: NONE	SHEET: 3 OF 4

REV:	DATE:
В	AUG 17 2006

NOTES!

- 1. Item 4 Star is **not** supplied with Hexashield Order Number 09.
- 2. The DS option, illustrated below, is for a Drilled Star that is available on sizes 15 to 25 only. This option is to allow unshielded wires to pass through the assembly.




STAR SIZE	15	17	19	21	23	25
ØD MAX	3.0	6.0	9.0	12.0	15.0	18.0
	[0.12"]	[0.24"]	[0.35"]	[0.47"]	[0.59"]	[0.71"]

3. Where the ferrule quantities required are standard, the item 4 - Star - is also standard. If the optional quantity is selected then 2 items 4 will be supplied - one "split" and the other one standard. See below for illustration.

EXAMPLE: FERRULE QUANTITY CODE -A13

-A13 = -A10 SPLIT STAR + -A3 STANDARD STAR



4. Assembly is to be permanently marked with Code Identity Number and Part Number. (e.g. 06090 HEX41-AB-00-21-A9-1)

tyco	Electronics
------	-------------

Wire and Harnessing Products

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCH DIMENSIONS ARE SHOWN IN BRACKETS

DRAWN: DATE: **CRJ** MAR 00

Raychem Wire and Harnessing Products 300 Constitution Drive Menlo Park, CA 94025 USA

This drawing and the information set forth hereon is the property of Tyco Electronics and is to be held in trust and confidence. Publication, duplication, disclosure or use for any other purpose not expressly authorized in writing by Tyco Electronics is prohibited.

Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.

TITLE:

HEXASHIELD ADAPTOR FOR CODE 41 CONNECTORS-PLAIN CLAMPING NUT

DOCUMENT NO.

HEX41-AY-YY-YY-AYY-1-YY

FILE-UK: File & DCR# SCALE: SHEET: Hex41-1scd-us D060249

NONE

4 OF 4