

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL REL PER LC20-0051-21	24MAY2021	RS	JO
	A1	ECN-22-143143	17JUN2022	BN	JO

NOTE:
1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.




Fig. 2




Fig. 4

Catalog No.	Part No.	Connection Type		Main			Tap			Dimensions in mm (in)		Tap Nut	Eye bolt material	Plating	Fig.
		Main	Tap	Diameter in mm (in)	AAC/CU	ACSR	Diameter in mm (in)	AAC/CU	ACSR	A	C				
THLB-400-4/0	EN4520-233	CU	CU	4.11-18.92 (0.162-0.745)	#6 - 400	#6 - 397.5	3.86-17.32 (0.152-0.682)	#6 - 4/0	#6 - 3/0	183.0 (7.20)	56.6 (2.23)	7/16	SS	None	2
THLB-400-4/0-P	EN3750-564	CU	CU	4.11-18.92 (0.162-0.745)	#6 - 400	#6 - 397.5	3.86-17.32 (0.152-0.682)	#6 - 4/0	#6 - 3/0	183.0 (7.20)	56.6 (2.23)	7/16	SS	Tin plated	2
THLB-400-4/0-B	EN4520-227	CU	CU	4.11-18.92 (0.162-0.745)	#6 - 400	#6 - 397.5	3.86-17.32 (0.152-0.682)	#6 - 4/0	#6 - 3/0	183.0 (7.20)	56.6 (2.23)	7/16	Bronze	None	2
THLB-400-4/0-BP	EN4520-178	CU	CU	4.11-18.92 (0.162-0.745)	#6 - 400	#6 - 397.5	3.86-17.32 (0.152-0.682)	#6 - 4/0	#6 - 3/0	183.0 (7.20)	56.6 (2.23)	7/16	Bronze	Tin plated	2
THLB-400R-4/0	ER9364-000	CU	CU	4.11-18.92 (0.162-0.745)	#6 - 400	#6 - 397.5	3.86-17.32 (0.152-0.682)	#6 - 4/0	#6 - 3/0	181.0 (7.13)	92.0 (3.63)	9/16	SS	None	4
THLB-400R-4/0-P	ER9365-000	CU	CU	4.11-18.92 (0.162-0.745)	#6 - 400	#6 - 397.5	3.86-17.32 (0.152-0.682)	#6 - 4/0	#6 - 3/0	181.0 (7.13)	92.0 (3.63)	9/16	SS	Tin plated	4
THLB-400R-4/0-B	ER9366-000	CU	CU	4.11-18.92 (0.162-0.745)	#6 - 400	#6 - 397.5	3.86-17.32 (0.152-0.682)	#6 - 4/0	#6 - 3/0	181.0 (7.13)	92.0 (3.63)	9/16	SS	None	4
THLB-400R-4/0-BP	ER9410-000	CU	CU	4.11-18.92 (0.162-0.745)	#6 - 400	#6 - 397.5	3.86-17.32 (0.152-0.682)	#6 - 4/0	#6 - 3/0	181.0 (7.13)	92.0 (3.63)	9/16	Bronze	Tin plated	4

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAVI.S 24MAY2021	TE Connectivity			
		CHK J.GUPPY 24MAY2021				
		APVD J.OPEL 24MAY2021				
		PRODUCT SPEC				
DIMENSIONS: mm (in)		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
		0 PLC ± -		HOT LINE CLAMP COPPER ALLOY 400-4/0		
		1 PLC ± -				
		2 PLC ± -				
		3 PLC ± -				
4 PLC ± -		4 PLC ± -		SIZE A3		
ANGLES ± -		FINISH				
MATERIAL SEE TABLE		FINISH SEE TABLE		CAGE CODE 00779		
				DRAWING NO C-E00001674		
				RESTRICTED TO -		
				WEIGHT -		
				CUSTOMER DRAWING		
				SCALE NTS		
				SHEET 1 OF 1		
				REV A1		