


REVISIONS				
P	LR	DESCRIPTION	DATE	BY
A2		INITIAL RELEASE	14MAR2023	MIN AK



All dimensions in mm [Inches]
TE PN: 1768017-1
LABEL ACROSS: 5
PER SHEET QTY: 100

MATERIAL	YELLOW NYLON FABRIC
ADHESIVE TYPE	PERMANENT ACRYLIC
LINER	GLASSINE PAPER

TOLERANCES mm [INCH]		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
LABEL HEIGHT:	±0.3 [0.012]	0 PIC	±	0 PIC	±
LABEL WIDTH:	±0.3 [0.012]	1 PIC	±	1 PIC	±
NER WIDTH:	±0.6 [0.024]	2 PIC	±	2 PIC	±
VERTICAL REPEAT:	±0.8 [0.031]*	3 PIC	±	3 PIC	±
HORIZONTAL REPEAT:	±0.8 [0.031]*	4 PIC	±	4 PIC	±
FRONT POSITIONING:	±0.8 [0.031]*	FINISH	±		
LEFT MARGIN:	±0.4 [0.016]				
QUANTITY:	-0% -2% %				
*NON ACCUMULATING					

THIS DRAWING IS A CONTROLLED DOCUMENT.

DMN	M. NUTTALL	14MAR2023	NAME	EB1138 - HAND WRITABLE NYLON FABRIC LABELS
CHK	M. NUTTALL	14MAR2023	PRODUCT SPEC	TTDS-181
APVD	A. KEAN	14MAR2023	APPLICATION SPEC	
WEIGHT	0.055 g		SIZE	A2
CUSTOMER DRAWING			QAGE CODE	A00YM
			DRAWING NO	1768017-1
			SCALE	NTS
			SHEET	1 of 1
			REV	A2