

CUSTOMER DRAWING



HL 2020 E TECHNICAL SPECIFICATIONS

VOLTAGE: 120VAC / 60 Hz

OUTPUT: 1600 WATTS / 13.3 AMPS

TEMPERATURE: 120°-1150°F (50°-620°C)


POWER CORD: 6 FT LONG, RUBBER

HEATING ELEMENT: CERAMIC

DIMENSIONS: 9.96" LG x 3.37" W x 7.87" H

NET WEIGHT: 2.19 Lbs.

Raychem Application Equipment

 TE Connectivity			TITLE: STEINEL ELECTRONIC HEAT GUN			
Unless Otherwise Specified dimensions are in inches. [Metric dimensions are shown in brackets]			DOCUMENT No. HL2020E			
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	ANGLES: N/A ROUGHNESS IN MICRON	TE Connectivity Corporation reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.	REVISION: A	REVISION DATE: 01OCT2019	APPROVED BY: I. Myong	
DRAWN BY: G. Rositano	DRAWN DATE: 24SEPT2019	ECO NUMBER: ECO-19-015092	CAGE CODE : 06090	SCALE: None	SIZE: A	SHEET: 1 of 1