



While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this catalog, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.



Technical Data

Highest Voltage Um	kV	123
Lightning Impulse Voltage	kV	350
Length	mm	1560
Diameter over sheds (approx.)	mm	220
Flashover Distance	mm	1550
Creepage Distance (approx.)	mm	3100
Kit Weight approx.	kg	9.5
Max. Conductor Size Cu/Al approx.	mm ²	1600
Outer Diameter Cable Insulation	mm	≤90
Outer Diameter Cable Oversheath	mm	≤110

OUTDOOR – TERMINATION
 TEMPORARY USE – 123 kV
 HEAT SHRINKABLE
 FOR XLPE – CABLE

OHVT-123H
 Offer drawing



TE Connectivity Ltd.
Raychem High Voltage Cable Accessories

TYCO DRAWING NO.:
 EPD-204-714-00

SHEET 1 OF 1 REV D