## HT - 200 Clear Fluoropolymer, Very Flexible, Flame-Resistant, Fluid-Resistant, Heat-Shrinkable




Table 1: <u>Dimensions</u> mm(inches)

Size	As Supplied Inside Diameter Minimum (D)		Recovered									
			Inside Diameter Maximum (d)		Wall Thickness (W)							
					Minimum		Maximum		Nominal			
	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.		
3/64	1.17	.046	0.58	.023	0.20	.008	0.30	.012	0.25	.010		
1/16	1.60	.063	0.79	.031	0.20	.008	0.30	.012	0.25	.010		
3/32	2.36	.093	1.17	.046	0.20	.008	0.30	.012	0.25	.010		
1/8	3.17	.125	1.57	.062	0.20	.008	0.30	.012	0.25	.010		
3/16	4.74	.187	2.36	.093	0.20	.008	0.30	.012	0.25	.010		
1/4	6.35	.250	3.17	.125	0.23	.009	0.38	.015	0.30	.012		
3/8	9.50	.375	4.74	.187	0.23	.009	0.38	.015	0.30	.012		
1/2	12.70	.500	6.35	.250	0.23	.009	0.38	.015	0.30	.012		
3/4	19.05	.750	9.50	.375	0.36	.014	0.51	.020	0.43	.017		
1	25.40	1.000	12.70	.500	0.41	.016	0.56	.022	0.48	.019		

**Color:** Tubing color is clear only.

Reference Specification TEC-108-120028

DIMENSIONS:		DWN	20JUN2018	MATERI	AL	_	FINISH			_	
INCHES		J. Bitter	_								
TOLERANCES UNLESS OTHERWISE SPECIFIED:		T. Licko APVD – T. Licko			TE Connectivity						
0 PLC 1 PLC 2 PLC	± - ± - ± -	PRODUCT SPEC TEC-108-	-120028	NAME	HT-200 SCD						
3 PLC	± - ± - ± -	APPLICATION SPEC	_								
4 PLC ANGLES		_		SIZE	CAGE CODE	DRAWING NO				RES	STRICTED TO
	$\oplus \Box$	WEIGHT		Α4	06090	C-HT	-200				_
		CUSTOMER D	RAWING				SCALE 1:1	SHEET	1 0	)F 1	REV A

TE Connectivity

2018