


SCD



MARKING ON MOULDED HOUSING:

1. MDCL 1 kNm
2. RAYCHEM
3. DATE CLOCKS

MARKING ON END FITTING:

1. YYWW

ELECTRICAL PROPERTIES

DRY AC FLASHOVER	:191 kV
WET AC FLASHOVER	:163 kV
DRY AC WITHSTAND	:143 kV
WET AC WITHSTAND	:141 kV
IMPULSE WITHSTAND VOLTAGE	:299 kV

NETWORK RAIL REFERENCES

121 / 563 / 001

MECHANICAL PROPERTIES


MAXIMUM WORKING LOAD (TOGETHER)	
BENDING	: 1 kNm
TENSION & COMPRESSION	: 10 kN
MINIMUM ULTIMATE STRENGTH (TOGETHER)	
BENDING	: 3 kNm
TENSION & COMPRESSION	: 30 kN
STL	:100 kN.

PHYSICAL PROPERTIES

NOMINAL CREEPAGE	: 1285 MM
NOMINAL DRY ARC	: 470 MM
END FITTING DESIGN	:CUSTOMER REQUEST
MATERIAL	
END FITTING	:STEEL GALVANISED
HOUSING	:RAYCHEM GREY EVA
CORE	:RBGF, ECR-GLASS
U-BOLTS	:STAINLESS STEEL

SHEET 1 OF 2

SCD



International Science
Centre, Block 1, National
Technology Park,
Castletroy,
Co. Limerick.

Raychem Insulator

DRN	DM	05/04	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 1 PLC ± 0.1 2 PLC ± 0.01 3 PLC ± 0.001 4 PLC ± 0.0001 ANGLES ± 1°	THIS DRAWING AND THE INFORMATION SET FORTH HEREIN ARE THE PROPERTY OF TE CONNECTIVITY AND ARE TO BE HELD IN TRUST AND CONFIDENCE. PUBLICATION, REPLICATION, REPRODUCTION OR USE FOR ANY OTHER PURPOSE NOT EXPRESSLY AUTHORIZED IN WRITING BY TE CONNECTIVITY LTD IS PROHIBITED.	TITLE	RRA-52G-TUG-608-UK DULMISON DESC: DK10110/01		
CHECK	JM	05/04			PCN	768766-000	DRG NO	INS0605
APP	TC	05/04			REV	3		
SCALE	NTS							

4

3

2

1

D

C

B

A

