







Description				Material											
1	hexagon screw M12x55			steel 8.8, electro galvanized											
2	spring washer 24x13x2,5			spring steel, mechanically galvanized											
3	upper part HEL-4843 OT			high strength AL-alloy, corrosion-resistant, tin-plated											
4	lower part HEL-4843 UT			high strength AL-alloy, corrosion-resistant, tin-plated											
5	O-Ring			70 shore A											
Tolerances not specified according to DIN ISO 2768-1 m				BURR PROJECTION:		DEBUR AND BREAK SHARP EDGES		DO NOT SCALE DRAWING		REVISION: 1, dated 18.01.2013					
				FORM BOUND MEASURE:		DIMENSION:		This Information is confidential and proprietary to Tyco Electronics Corporation and it's subsidiaries and affiliates. It may not be disclosed to anyone, other than Tyco Electronics personnel, without written authorization from Tyco Electronics Corporation, Harrisburg, Pennsylvania USA.							
				NOT FORM BOUND MEASURE:		mm									
	NAME	SIGNATURE	DATE	MATERIAL:				DESCRIPTION:							
DRAWN	T. Scholze		04.09.2007					AL Flat Direct Terminal Clamp HEL-4843; RPN: 666398-000 2x 35-150 mm²							
CHK'D	M. Dolling		04.09.2007												
APPV'D															
 Tyco Electronics Tyco Electronics Raychem GmbH Werk Falkenberg Heilsternstr. 1 04895 Schmerkendorf (Germany)				SURFACE:				DWG NO.		4843		A4			
				WEIGHT:				112g		SCALE:		1:1		SHEET: 1 OF 1	