

4

3


2

1

© 2020 TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	2	REDRAWN PER ECO-21-004049	19OCT2020	MR	KP



ELECTRICAL PROPERTIES :

DRY AC FLASHOVER : 163 kV
WET AC FLASHOVER : 120 kV
DRY AC WITHSTAND : 146 kV
WET AC WITHSTAND : 106 kV
IMPULSE WITHSTAND VOLTAGE : 219 kV

MECHANICAL PROPERTIES :

SCL : 12.5 kN
MDCL : 5.5 kN
STL : 25 kN

PHYSICAL PROPERTIES :


NOMINAL CREEPAGE : 922 MM
NOMINAL DRY ARC : 300 MM
END FITTING DESIGN : STANDARD ANSI 29.7 & IEC60720 DESIGN

MATERIAL :


END FITTING : STEEL GALVANISED
HOUSING : RAYCHEM HV RED (EVA)
CORE : RBGF

DIFFERENT THREAD TYPES AVAILABLE
STANDARD PINS SUPPLIED ON REQUEST

MARKING ON ENDFITTING
1. INS0986
2. MDCL : 5.5kN
3. RYC



CN2508-000
PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.RAJ 19OCT2020		 TE Connectivity								
		CHK K.PUSTHAY 19OCT2020										
		APVD K.PUSTHAY 19OCT2020										
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RLP-36R-VG-M20NPG-M-0.40S								
		0 PLC ±		SIZE A3			CAGE CODE 00779		DRAWING NO C-INS0986		RESTRICTED TO -	
		1 PLC ±										
		2 PLC ±										
		3 PLC ±										
4 PLC ±		PRODUCT SPEC										
		APPLICATION SPEC										
MATERIAL SEE NOTES		FINISH N/A		WEIGHT								
CUSTOMER DRAWING						SCALE NTS		SHEET 1 OF 1		REV 2		