

4

3

2

1

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT - TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ORIGINAL ISSUE	20MAR2020	GR	KP



NOTES:

- 1) UNSPECIFIED TOLERANCE
 $\pm(0.04 \times d + 1.5)\text{mm}$ WHEN $d < 300\text{mm}$
 $\pm(0.025 \times d + 6)\text{mm}$ WHEN $d > 300\text{mm}$
 WITH MAX. TOLERANCE OF $\pm 50\text{mm}$

PRODUCT MARKINGS:

1. DATE DIAL
 2. TE LOGO
 3. SCL XX kN
 4. BATCH NO #

MATERIALS:

1. CORE : ECR FIBERGLASS REINFORCED POLYMER
 2. HOUSING : SILICONE RUBBER
 3. END FITTINGS : HOT DIP GALVANISED STEEL
 4. TEST STANDARDS : IEC 61109 & IEC 61952

TCPN	Description	Creepage distance (mm)	Dry arc distance (mm)	No. of Sheds	Dry FO (kV)	Dry withstand (kV)	Wet FO (kV)	Wet withstand (kV)	Imp FO (+ve) (kV)	Imp W/S (+ve) (kV)	SCL (kN) (kV)	STL (kN) (kV)	Section Length L(mm)	APPROX WEIGHT (kg)
EP4979-000	CLP-11-FM20-200-659-M	659	314	7	120	105	105	100	215	200	11	25	426	3.9

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 20MAR2020

GHANSHYAM

CHK 20MAR2020

RAJESH

APVD 20MAR2020

K PUSTHAY

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME
GENERIC LINE POST SERIES -38.1mm FRP

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=INS1786	—

SCALE	SHEET	1 OF 1	REV
NTS			A