





REV. A
DC0 81131

COIL: @ 25°C
RESISTANCE 98 OHMS ±10%
NOMINAL VOLTAGE 6.0 VDC
MUST OPERATE 3.5 VDC
MUST RELEASE 2.0 VDC MAX, 0.28 VDC MIN.

ENVIRONMENT:
VIBRATION 10 Hz TO 3000 Hz @ 30 g's
SHOCK 75 g's 6 MS. DURATION
TEMPERATURE -65 °C TO +125 °C
NOTES: OPERATE TIME 2.0 MS MAX
RELEASE TIME 4.0 MS MAX
CONTACT STABILIZATION 2.5 MS MAX

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1 AMP
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.F. 05/07/12 CK. J.M.B. 05/07/12

TE Connectivity

CUST. QPL
CUST. NO. M39016/18-032M REV.

TE NUMBER
"JMGAD" RELAY

CII PART NUMBER
JMGACD-6M