

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	01.04.2020	SI	SI

KAPTON LABELS OVERVIEW



SERIES	PART NO.	DESCRIPTION	MATERIAL	TTDS
T1K	D01425-000	T1K-127127-10-9	KP228, Kapton white gloss (0,063 mm), Acrylic adhesive	TTDS-034

Quantity per roll: 10.000 PCs

Labels across: 5

Winding: outside






length of roll: 31,8 m



KAPTON SERIES

All dimensions in mm [inch]

labels are centered on the liner as long as not declared separately

LABEL BUILD DETAILS		TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT		DWN S. Iser / 01.04.2020 DATE		TE Connectivity	
	SUBSTRATE	LABEL HEIGHT:	±0,3 [012]	 DIMENSIONS mm [INCHES] TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	CHK S. Iser / 01.04.2020 DATE	 Name Kapton Label Size „127127“			
	ADHESIVE	LABEL WIDTH:	±0,3 [012]		APVD S. Iser / 01.04.2020 DATE				
	LINER	WEB WIDTH:	±0,8 [031]		PRODUCT SPEC DATE				
		VERTICAL REPEAT:	±0,8 [031]*		APPLICATION SPEC DATE				
		HORIZONTAL REPEAT:	±0,8 [031]*	WEIGHT T1K: 0,016 g	SIZE A3	CAGE CODE C2290	DRAWING NO. C-KAPTON	RESTRICTED TO	
		PRINT POSITIONING:	±0,8 [031]*	MATERIAL SEE TABLE	FINISH GLOSS UNPRINTED MATT PRINTED		CUSTOMER DRAWING		
		LEFT MARGIN:	±0,4 [016]				SHEET 1 of 1		
		QUANTITY:	-0% +2%				REV A1		
		*NON ACCUMULATING							